



| PART NO. | "A" REF. | "B" REF. | "C" HOLDING DIA. | "D" REF. |
|-------------|------------|-------------|---------------------|-----------|
| DHURCS-2-01 | .49[12.4] | .75 [19.0] | 1/8 [3.2] | .17 [4.3] |
| DHURCS-3-01 | .56 [14.2] | .89 [22.6] | 3/16 [4.8] | .24 [6.1] |
| DHURCS-4-01 | .64 [16.2] | 1.02 [25.9] | 1/4 [6.4] | .30 [7.6] |









NOTES:

1. MATERIAL: NYLON 6/6 (RMS-01).
FLAME RETARDANT NYLON (RMS-19)
AVAILABLE BY SPECIAL ODER.
TO ORDER, REPLACE "-01" WITH "-19"

2. COLOR: NATURAL.

| | DOUBLE HALF "U" ROUTING CLIP W/ MOUNTING SCREW OF ET DW | | | | | | |
|-----------|---|------------------|---------------|--|----------|-----------|-------|
| | CREATED USING SOLIDWORKS | FILE #: DHURCS | | DWN: SM | APP: DJZ | FINAL | |
| Ī | TOLERANCES | SHEET: 1 OF 1 | SHEET SIZE: A | DT: 01/22/04 | CHKD: SJ | PART# | PRINT |
| /04 TE | UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC.=±1/64 ANG.=±1° | RE: RICHCO, INC. | | RICHCO, INC. ENG@RICHCO-INC.COM (773) 539-4060 | | SEE TABLE | CA |

| Α | RELEASED FOR PRODUCTION | SM | 01/22/04 |
|------|-------------------------|-------|----------|
| REV. | DESCRIPTION | ENGR. | DATE |