
Customer Information



HARW!M

04 SIGNAL CONTACTS AND 02 LEFT (AFTER No.1) SPECIAL CONTACTS,

M80-263F202-04-02

DIM 'A' = 30.00mm, DIM 'B' = 25.00mm

CONNECTOR WITH NO SIGNAL CONTACTS, AND 06 SPECIAL CONTACTS.

M80-263F206-00-00

DIM 'A' = 34.00mm, DIM 'B' = 29.00mm

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES X. = ±1mm X.X = ±0.50mr $X.XX = \pm 0.20$ mm $X.XXX = \pm 0.01$ mm

MATERIAL: FINISH:

SINGLE SPECIAL CONTACT HAS EQUIVALENT FOOTPRINT OF 4 SIGNAL CONTACTS.

EACH MOULDING CAN HOUSE A MAXIMUM OF 50 SIGNAL CONTACTS PROVIDING THERE ARE NO SPECIAL CONTACTS, OR 12 SPECIAL CONTACTS PROVIDING

THERE ARE NO SIGNAL CONTACTS, AND ALL CONFIGURATIONS BETWEEN.

IF THERE ARE NO SIGNAL CONTACTS, USE ONLY THE FIRST SPECIAL CONTACT QTY

I.E. M80-263F2XX-00-00

SEE ABOVE

JACKSCREW DATAMATE MIXED TECHNOLOGY FEMALE CRIMP MOULDING WITH HARDWARE

CHECKED:

CUSTOMER REF.:

ASSEMBLY DRG:

DRAWN:

APPROVED: R.ALEXANDER

R.PORTLOCK

R. PORTLOCK

OF.

DRAWING NUMBER:

M80-263F2XX-XX-XX

www.harwin.com technical@harwin.com

ANGLES = ±5° UNLESS STATED

SEE ABOVE S/AREA: