







REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	MAR 01/18	L.CHAN




FRONT VIEW



SIDE VIEW



RECOMMENDED PANEL CUTOUT



RECOMMENDED PCB LAYOUT (COMPONENT SIDE OF BOARD)



MATERIALS:

HOUSING: ENGINEERING THERMOPLASTIC. BLACK.
FLAMMABILITY RATING UL 94V-0

CONTACTS: PHOSPHOR BRONZE
PLATING: SELECTIVE GOLD PLATING ON MATING SURFACE.
SEE PART NO. FOR THICKNESS.
50u" [1.27 MICRONS]
MIN. NICKEL UNDERPLATE.
100u" MIN. MATTE TIN OR GOLD FLASH
ON CONTACT AISLS.

PART NUMBER: RJSAE-X080-02

GOLD PLATING OPTION —
D = 6u" GOLD PLATING
G = 15u" GOLD PLATING
J = 30u" GOLD PLATING
5 = 50u" GOLD PLATING

UNLESS SPECIFIED OTHERWISE	DRAWN	RONNIE.C	DATE	MAR 01/18	Amphenol Canada Corp.				
PRIMARY UNITS INCH	CHECKED	AMY.Z		MAR 01/18	www.amphenolcanada.com				
SECONDARY MILLIMETER	M.E. APP'D		TITLE			2X1 STACKABLE MODULAR JACK, 8 POSITION, 8 CONTACTS, 2-PIECE CONSTRUCTION, WITHOUT SHIELD, WITHOUT LED – RoHS COMPLIANT			
REFERENCE IN PARENTHESES	Q.A. APP'D								
GENERAL TOLERANCES	DWG APPR.		DWG. NO.			P-RJSAE-X080-02			REV A
1 DECIMAL PLACE	ENG. REL. NO.								
2 DECIMAL PLACES	REF.	EAR# RJ18044							
3 DECIMAL PLACES ±0.015	THIRD ANGLE PROJECTION		DO NOT SCALE DRAWING						
ANGULAR DEGREES ±1.0°				CODE ID No. 03554	DWG SIZE: C	SCALE: N/A	SHEET 1	OF 1	

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.