









PANEL CUT FOR INSERTS FOR USE
WITHOUT HOODS/ HOUSINGS

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APV
	A	INITIAL	08MAY2015	DW	CW
	B	ECR-15-013292	24SEP2015	DL	CW
	C	ECR-21-105887	26JUL2021	BS	CW


NOTES:

- NOTES:
1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 250 V
RATED CURRENT: 10 A
INSULATION RESISTANCE: $\geq 400\text{M}\Omega$
RATED IMPULSE VOLTAGE: 2.5 KV
POLLUTION DEGREE: 2
CONTACT RESISTANCE: $\leq 5\text{ m}\Omega$
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)
CONTACT TYPE: CRIMP CONTACT
 2. CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20200X20XX000)

注释：

1. 技术参数：
- 绝缘材料：PC
 - 额定电压：250V
 - 额定电流：10A
 - 绝缘电阻： $\geq 400M\Omega$
 - 额定脉冲电压：2.5 KV
 - 污染等级：2
 - 接触电阻： $\leq 5 m\Omega$
 - 阻燃等级：UL94V-0
 - 插拔次数：500次
 - 接线范围：0.14-2.5 mm²（26-14 AWG）
 - 接线类型：冷压接
2. 端子需要单独订购，
（订货号参考图面：T20200X20XX000）

HDD-072-F 73-144	T2031442201-000
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN David Wang 08MAY2015	 TE Connectivity			
DIMENSIONS: mm		CHK Chris Wang 08MAY2015	NAME HDD-072-F 73-144			
		APVD Xiang Xu 08MAY2015				
		PRODUCT SPEC 108-137043				
		APPLICATION SPEC 114-137043				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		WEIGHT -	A3	00779	C=T2031442201000	-
MATERIAL -		Customer Drawing		SCALE 1:1	SHEET 1 OF 1	REV C