



NOTE:

1. CABLE: (28AWGX9C)AL-FOIL SHIELD WITH A DRAIN WIRE, PVC JACKET, NON-UL, COLOR: GRAY(K103) O.D.= $\phi 4.8 \pm 0.15$ mm
 JACKET PRINTING WORD: **BELKIN**® Belkin Pro Series For Optimum Data Transfer www.belkin.com U.S. Patent No. Des. 396,689
2. D-SUB 9 PIN FEMALE (DE9S): SOLDER TYPE, GOLD FLASH CONTACTS, BLACK PBT INSULATOR, TIN PLATED SHELL, MOLDED TOOLING: M $\frac{1}{2}$ -D09-HOX, BIG SIDE MOLDED LOGO " **BELKIN** "; SMALL SIDE MOLDED LOGO " F2N209-XX ".
3. D-SUB 9 PIN MALE (DE9P): SOLDER TYPE, GOLD FLASH CONTACTS, BLACK PBT INSULATOR, TIN PLATED SHELL WITH GROUND INDENT, WITH FEMALE SCREW LOCK 4.75*5*11.3mm (#4-40UNC) & SPRING WASHER & 4.75*1.6mm (#4-40UNC) HEX NUT, MOLDED TOOLING NUMBER: M $\frac{1}{2}$ -D09-HOX, BIG SIDE MOLDED LOGO " **BELKIN** "; SMALL SIDE MOLDED LOGO " F2N209-XX ".
4. SHIELD: WITH AL-FOIL SHIELD.
5. HOOD: CONNECTOR MOLDED PVC GRAY(K103).
6. THUMBSCREW: HDE15P WITH 5X42-1 T.S. (#4-40UNC) SCREW, BLACK ZINC PLATED, MOLDED PVC GRAY(K103).

PIN	OUT
DE9S	DE9P
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9
SHELL	DRAIN WIRE
	SHELL

P/N	L	T	SMALL SIDE LOGO (DE9P & DE9S)
F2N209x06	1830	50	F2N209-06
F2N209x10	3050	50	F2N209-10

Part # F2N209xXX	SPRAL MSE/PC MTR EXT CBL
Seq# N/A	DB9M/DB9F; SH
Drawn by: WAY	Date: 06-01-900
Approved by: PAW	Date: 06-01-900
Page 1 of 1	Revision A.

