



4

3


2

1

LOC J	DIST —	REVISIONS 變更					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	RELEASED	20FEB2015	Z.S	N.Y



A-A B-B



- NOTE:
- 1.GENERAL TOLERANCE: ±0.25
 - 2.MATERIAL: COPPER ALLOY, FINISH: OVER NI PLATING 1.27um MIN.
(CONTACT AREA) 0.76um MIN GOLD PLATING
 - 3.APPLICABLE WIRE: AWG#22-#20 (INS DIA ø1.58~ø2.56)

25.5	12.75	1-2288019-1
21.8	9.05	2288019-1
L4	L1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位： 耗
mm

MATERIAL
材料
SEE NOTE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -

FINISH
仕上
SEE NOTE

DWN
Z.SHEN
20FEB2015

CHK
M.HARASAWA
20FEB2015

APVD
N.YAMASAKI
20FEB2015

PRODUCT SPEC
製品規格
108-78182

APPLICATION SPEC
取付適用規格
114-5369

WEIGHT
—

TE Connectivity

NAME
名称
DYNAMIC D4200 W-W
TAB CONTACT SS SIZE L/P

SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
A3	00779	C-2288019	—

CUSTOMER DRAWING

SCALE
尺度 5:1

SHEET
1 OF 1

REV
A