

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By TE Connectivity

ALL RIGHTS RESERVED.

LOC
HBDIST
—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
C		REACTIVE PN ECO-13-005804	21May2013	YS.H	BH.Y
D		CHANGE RAW MATERIAL OF CARD ECO-19-012552	14-AUG-19	TOD	K.T








Diagram dimension	Tolerance
max. 1mm	±0.1mm
1 - 3mm	±0.2mm
min. 3mm	±0.3mm

DRILLING DIAGRAM
BOTTOM VIEW (2/1)CONNECTION DIAGRAM
BOTTOM VIEW (2/1)

NOTE

① 1.LOT NO. SYSTEM AS FOLLOWING:

WEEK
YEAR

② 2.TERMINAL DIMENSIONS BEFORE SOLDER DIP

③ 3.FOR THE TIN-PLATING OF THE PINS: +0.1mm FOR WIDTH, THICKNESS AND DIAMETER
+0.5mm FOR LENGTH

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mmTOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL

FINISH

DWN

K.Okada

CHK

H.Sasaki

APVD

A.Nagai

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

CUSTOMER DRAWING

TE

TE Connectivity

NAME

SDT-LMR2 CUSTOMER DRAWING

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1461100

SCALE 4:1

SHEET

1 of 2

REV

D

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By TE Connectivity

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

HB

-

P

LTR

DESCRIPTION

DATE

DWN

APVD

-

SEE SHEET 1

-

-

-

Ⓢ

Ⓢ

Ⓢ

Ⓢ

Ⓢ

Ⓢ


SDT-S-124LMR2	2-1440009-6	108-79452	STANDARD	f
SDT-S-112LMR2	1440003	108-79451	STANDARD	e
SDT-S-109LMR2	9-1419125-5	108-79450	STANDARD	d
SDT-S-106LMR2	5-1440007-0	108-79449	STANDARD	c
SDT-S-105LMR2	8-1419125-3	108-79448	STANDARD	b
SDT-S-103LMR2	1461100-1	108-79447	STANDARD	a
DESCRIPTION	TE PART NO	PRODUCT SPEC	DESCRIPTION	No.

RELAY TYPE

		EPOXY RESIN	SEAL (BASE & TERMINAL)	15
		EPOXY RESIN	SEAL (BASE & YOKE)	14
		3UEW	MAGNETIC WIRE	13
94V-0		P.B.T	CASE	12
94V-0		P.B.T	BOBBIN	11
	SOLDER DIP	C.P WIRE	COIL TERMINAL	10
94V-0		PPS	CARD	9
		AgSnO	MOVABLE CONTACT	8
		AgSnO	NO.CONTACT	7
		STEEL	HINGE SPRING	6
	SOLDER DIP	Cu ALLOY	NO.TERMINAL	5
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	4
	NIP	STEEL	CORE	3
	NIP	STEEL	ARMATURE	2
	NIP	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

-

DWN
K.Okada

CHK
H.Sasaki

APVD
A.Nagai

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

SDT-LMR2 CUSTOMER DRAWING

SIZE
A3

CAGE CODE
00779

DRAWING NO
C=1461100

RESTRICTED TO
-

SCALE
4:1

SHEET
2 of 2

REV
D

1470-19 (3/11)