






ISS.	AMEND	DATE
1	ISSUED	01/03/21




Ø3.20 PLAIN HOLE
CP30620SMBX1



2x HOLE VARIANTS
Ø3.2mm CSK 90° x Ø5.85
PLAIN Ø3.2 HOLES



- Material:
1. RJ45 In-Line Coupler:
Black PC or ABS, UL94 V-0 Fully Shielded
 2. RJ45 In-Line Coupler Contact:
Phosphor Bronze, 3-50 micro inches
gold plating over nickel plate.
 3. PCB: FR4, UL94 V-0
 4. FT Frame: Zinc Diecast, Black



- Performance:
1. T568A & T568B wiring.
 2. Meet ISO/IEC 11801 and EN50173
 3. Meet ANSI/TIA/EIA 568B.2
 4. Operating Temperatures: Min -10°C Max +70°C

VARIANTS

PART NO.	HOLE DETAILS
CP30620SMB	HOLE Ø3.2 x CSK 90° x Ø5.85
CP30620SMBX1	PLAIN HOLE Ø3.2

RoHS
COMPLIANT

TOLERANCE

NO DEC. PLACE ±
1 DEC. PLACE ±
2 DEC. PLACE ±
HOLE Ø ±
ANGLES ±
UNLESS
OTHERWISE STATED

Cliff Electronic Components Ltd.

76 Holmethorpe Avenue, Holmethorpe Industrial Estate,
Redhill, Surrey, RH1 2PF, England, UK
Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED
TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK. © 2021

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.

MATERIAL: See Notes

FINISH: See Notes

DRAWN: T.J.O.

APPROVED: D.P.J.

3rd ANGLE PROJECTION:

TITLE: FRONT MOUNT BLACK METAL SLIM FT FTP CAT5e RJ45 SHIELDED

DRWG. No. CP30620SMB

FORM: A4DRWGH