

COMPONENTS					
5	GROUNDING SPRING	2			
4	LATCH	1			
3	INSERT MODULE	1			
2	JACK REAR HOUSING	1			
1	JACK FRONT HOUSING	1			
ITEM	PART NAME	Q'TY			

TRANSMISSION PERFORMANCE Meet all requirements specified in channel requirement of ISO/IEC 11801,Class EA ANSI/TIA-568-C.2 Category 6A

ELECTRICAL Electrical Insulation Resistance : 500 $M\Omega$ min. @ 100V d.c

Dielectric Withstanding Voltage:
1000V d.c. or a.c. Peak; one contact to all other contacts connected together @ 60Hz for 1 minute. 1500V d.c. or a.c. Peak; all contacts connected together to shield @ 60Hz for 1 minute.

DATE

11/5/20

Α0

Released

APP'D. BY

AB

MECHANICAL


Insertion / Extraction Life: 750 Cycles Minimum

PHYSICAL

Housing: Zinc—alloy fully shielded
Spring Wire: Phosphor Bronze Alloy Plated With
50 micro—inch of Gold


SS-82120-003

PART NUMBER









DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE

DIMENSIONS: METRIC

UNLESS OTHERWISE SPECIFIED

TOLERANCES ARE ±0.2 ANGLES ARE ± 1°

1 OF 1

206 Van Vorst Street Jersey City, NJ 07302 +1 201 432 0463 http://www.belfuse.com

CAT 6A SHIELDED KEYSTONE COUPLER JACK

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREO ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF BEL FUSE, INC. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTE CONSENT OF BEL FUSE, INC.

ON	DRN BY:		DATE 10/28/20		
)F En	APPD BY:	AB	DATE 11/5/20		20
-11	DWG NO.	CT820038		REV.	Α0