




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/30/2020	MBLACKWOOD
B	ECN 10939 CORRECT CONNECTOR DESCRIPTIONS	01/19/2021	MBLACKWOOD





RECOMMENDED
PANEL CUTOUT



PIN 1

2X MINI DISPLAYPORT
FEMALE CONNECTOR





PIN OUT

P1	P2	P1	P2
1	1	13	13
2	2	14	14
3	3	15	15
4	4	16	16
5	5	17	17
6	6	18	18
7	7	19	19
8	8	20	20
9	9	S	S
10	10		
11	11		
12	12		

NOTES:

- ELECTRICAL TEST:
 - COMPONENT SHALL NOT HAVE ANY OPEN/SHORT, MISWIRING OR INTERMITTENT FAILURES.
 - COMPONENT SHALL BE TESTED FOR CONTINUITY.
 - VOLTAGE TEST: DC 300V 10MS;
INSULATION RESISTANCE: 10.0M ohm/min;
CONDUCTOR RESISTANCE: 2.0 ohm/max.
- ALL DIMENSIONS ARE FOR REFERENCE ONLY.
- COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN A CLEAR POLYBAG AND LABELED PER L-COM SPEC LSP-010-2.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [.5] ANGLES ±1° .XXX = ±.005 [.13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DFRISIELLO	09/22/2020	
APPROVED BY MBLACKWOOD	09/30/2020	CATEGORY VIDEO	
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION MINI-DP F TO MINI-DP F CONVERTOR (KEYSTONE PANEL MOUNT)	
COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	ITEM NO. VPC00001
SCALE: NONE		CAD FILE: VPC00001.SLDDRW	
SHEET 1 OF 1			REV. B