





This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.

Customer drawing

REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
1	HK--	First Release Drawing	05/26/08	IP
2	HK--	Update The Drawing	04/12/13	IP
3	HK--	Update The Drawing	01/21/15	IP

D-SUB TECHNICAL DATA

SHELL : Steel, 100u" Tin Over 50u" min nickel over 50u" min Copper
BODY : Glass-Filled Thermoplastic PBT,UL94V-0,Black
CONTACTS : Copper alloy
Gold flash over 50u" nickel on mating area
100u" tin over 50u" nickel on termination area
Rear Nut : Brass, Nickel Plated.
ELECTRICAL : Voltage rating 250 VAC/Rms 60Hz
Current Rating :3 AMP
Withstanding Voltage >1000 VAC Rms
Insulation resistance >1000 M Ohms
Contact resistance 20 mOhms max
MARKING : Amphenol...(Series No.)
Commercial reference
Manufacturing date




Dimensions

Positions	A	B	C	E	F
9	30.81	24.99	16.33	11.08	10.16
15	39.20	33.30	24.70	19.39	17.78
25	53.05	47.04	38.40	33.24	30.48
37	69.40	63.50	54.80	49.86	45.72

PRODUCT CODE

L 17D X FR D A XX S



UNLESS OTHERWISE SPECIFIED TOLERANCES U.S. METRIC .X +/- 0.50 .XX +/- 0.30 .XXX +/- 0.20 FRACTIONS +/- ANGLES +/- 5° FOR MATERIALS AND FINISHES SEE NOTES REMOVE SHARP EDGES DIMENSIONS U.S. INCHES METRIC MM	APPROVAL		DATE	Amphenol Amphenol East Asia Limited TITLE IDC Flat Cable D-SUB Series SIZE DRAWING NO. A4 L17DXFRDAXXS SCALE NONE SHEET 1 OF 1	
	DRAWN	Peliss Liu	01/21/15		
	CHECKED	Tony Tang	01/21/15		
	CHECKED				
DRAWING FILE :				ANGLE OF PROJECTION	
				REV. 3	