



THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION
MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING
PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

REVISIONS				
SYM	ZONE	ECN, ERN NO.	DATE	APPRD.
A		RELEASE DWG PER ECN E07122	APR26.07	L.C
B		PROPOSAL	MAR 4.07	L.C

NOTES:

1. MATERIALS:

CONTACTS:

COPPER ALLOY.
GOLD PLATING ON MATING AREA ,REFER
TO AMPHENOL PART NUMBER OPTION.
50u" NICKEL PLATED UNDERPLATE ALLOVER.
100u" TIN PLATED SOLDER AREA.

FRONT & REAR SHELLS: STEEL, 0.35 [.014] THICK.
FRONT & REAR SHELL NICKEL PLATED.

HOUSING BODY
& COVER: PBT, GLASS FILLED,
FLAMMABILITY UL94V-0.
COLOUR: REFER TO AMPHENOL
PART NUMBER OPTION.

2. TOLERANCE UNLESS INDICATED OTHERWISE: ± 0.30 [.012].



AMPHENOL P/N: UE28-AMX4-XX0

<u>CONTACT PLATING</u>	
5=[0.76 MICRONS]	30u" GOLD
7=[0.08 MICRONS]	3u" GOLD

COLOUR
1=BLACK
2=BEIGE

SHELL STYLE _____
2=SMALL REAR CLAMP
3=LARGE REAR CLAMP (STANDARD)

SEE SHEET 2 FOR SHELL DETAILS

DRAWN	MT.CHEN	DATE	APR26.07			
DESIGNED	MT.CHEN	APR26.07	Amphenol Canada Corp.			
CHECKED	L.CHAN	APR26.07	TITLE			
I. E. APPRD.			UNIVERSAL SERIAL BUS (SERIES A) PLUG,			
Q. A. APPRD.			SOLDER CUP, 4 CONTACTS-ROHS COMPLIANT			
DWG. APPRD.						
ENG. REL. NO.			DWG	DRAWING NO.		REV.
REF. ECN E07122			C	P-UE28-AMX4-XX0		B
DIMENSIONS ARE IN		CODE ID. NO.	SCALE	WT.	SURF.	SHEET
mm/INCHES		03554	3/1	-----	-----	1 OF 2

