


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 5802: CHANGED VALUES TO 0-4 GHz, REVISED PACKAGING NOTE	11/2/11	D.FRISIELLO

DESCRIPTION	MATERIAL	FINISH
CENTER PIN	BRASS	GOLD
BODY	BRASS	NICKEL
WASHER	BRASS	NICKEL
NUT	BRASS	NICKEL
GASKET	RUBBER	--
CRIMP FERRULE	BRASS	NICKEL
INSULATOR	TEFLON	---



**NOTES:**

**ELECTRICAL:**  
 IMPEDANCE: 50 OHMS  
 WITHSTAND VOLTAGE: 1500V  
 FREQUENCY RANGE: 0-4 GHz  
 VSWR: ≤1.30 @ 0-4 GHz  
 DURABILITY: ≥ 500 CYCLE  
 CABLE RETENTION: > 40 POUNDS

**MISCELLANEOUS:**  
 COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

APPLICATION: RG58, LMR195 AND EQUIVALENT.

ALL DIMENSIONS ARE FOR REFERENCE ONLY.

**RoHS Compliant** ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY B.PUCHASKI	2/25/10		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ±.005	CHECKED BY M.AUDAS	2/25/10	CATEGORY <b>CONNECTOR</b>	
	APPROVED BY M.AUDAS	2/25/10	PRODUCT DESCRIPTION <b>Reverse Polarity TNC Jack Bulkhead Crimp for RG58 / WBC195 / LMR195 Series</b>	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>
			DWG. NO. <b>ARTJ-3702</b>	REV. <b>E</b>
			SCALE: NONE	CAD FILE: ARTJ-3702.SLDDRW
				SHEET 1 OF 1