


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2165712002](#)
Status: **Active**
Overview: [Micro-Fit+ Connector System](#)
Description: Micro-Fit+ Vertical Header, 3.00mm Pitch, Single Row, 2 Circuits, 0.38µm Gold (Au) Plating, UL 94V-0, Glow-Wire Capable, Black



Documents:
[Drawing \(PDF\)](#) [Test Summary 2157590005-TS-000 \(PDF\)](#)
[Product Specification 2064600000-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification 2165710002-PK-000 \(PDF\)](#)

General
Product Family PCB Headers
Series [216571](#)
Application Power, Wire-to-Board
Overview [Micro-Fit+ Connector System](#)
Product Name Micro-Fit+
UPC 193264926763

Physical
Breakaway No
Circuits (Loaded) 2
Circuits (maximum) 2
Color - Resin Black
Durability (mating cycles max) 200
First Mate / Last Break No
Glow-Wire Capable Yes
Keying to Mating Part Yes
Lock to Mating Part Yes
Material - Metal High Copper Alloy
Material - Plating Mating Gold
Material - Resin Liquid Crystal Polymer
Net Weight 0.351/g
Number of Rows 1
Orientation Vertical
PCB Thickness - Recommended 1.57mm
Packaging Type Tray
Pitch - Mating Interface 3.00mm
Pitch - Termination Interface 3.00mm
Plating min - Mating 0.381µm
Polarized to Mating Part Yes
Polarized to PCB Yes
Shrouded Yes
Temperature Range - Operating -40° to +105°C
Termination Interface: Style Through Hole

Electrical
Current - Maximum per Contact 12.5A
Voltage - Maximum 600V AC (RMS)/DC

Material Info

Reference - Drawing Numbers
[Packaging Specification 2165710002-PK-000](#)
[Product Specification 2064600000-PS-000](#)
[Sales Drawing 2165710003-SD-000](#)
[Test Summary 2157590005-TS-000](#)

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[216571 Series](#)

This document was generated on 07/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION