








SHEET DESCRIPTION	
BLADE CONNECTOR ASSEMBLY	

DESCRIPTION	DIMENSIONS		
	A	B	C
2X2	TBD	TBD	TBD
2X3	TBD	TBD	TBD
2X4	12.46	1.75	27.9
2X6	15.96	1.75	32.7
2X8	TBD	TBD	TBD
2X10	22.97	1.75	46.4



PRIMARY LOCK REINFORCER (PLR) SHOWN
IN PRE-STAGE POSITION

SECTION Z-Z



PRIMARY LOCK REINFORCER (PLR) SHOWN
IN FINAL-LOCK POSITION

SECTION Y-Y


SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex						
	mm		3:1													
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/01 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: KBORUSZEWSKI 2014/02/19 APPR: VKOSHY 2014/03/05					MX150 GEN 2 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL						
 = 0																
ANGULAR TOL ± 3.0 °				PRODUCT CUSTOMER DRAWING												
 = 0	4 PLACES ±									DOCUMENT NUMBER						
 = 0	3 PLACES ±									DOC TYPE						
 = 0	2 PLACES ± 0.1				DOC PART											
 = 0	1 PLACE ± 0.2				REVISION											
 = 0	0 PLACES ±				SD-160011-0001											
 = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
							A1-SIZE		160011				GENERAL MARKET		5 OF 11	

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:24
-----------------	----	--------------	---------------------


SHEET DESCRIPTION
BACKSHELL NOTES

BACKSHELL NOTES: VALID UNLESS OTHERWISE SPECIFIED


1. GENERAL:
- a. APPLICATION SPECIFICATION SEE: AS-34951-001
- DESIGNED TO MATE WITH BLADE SEALED ASSEMBLY
 - SPECIFIED IN MOLEX DRAWING SD-33482-0001
 - SYSTEM TO BE USED WITH WIRE WITHIN DIAMETER RANGE OF 1.2mm TO 2.69mm
 - COMPONENTS ARE OPTIONAL AND MUST BE PURCHASED SEPERATELY
 - DESIGN IS OWNED BY SCHLEMMER FOR SCHLEMMER BACKSHELL.
 - DESIGN IS OWNED BY MOLEX FOR MOLEX BACKSHELL.
 - 90° ADAPTOR DESIGN IS OWNED BY MOLEX.
 - FOR ADDITIONAL INFORMATION SEE THE BACKSHELL COMPONENT DRAWING SD-34950-0001




2X3




2X4




2X4



2X6



2X8



2X10

BACKSHELL CUSTOMER
MODEL NUMBER LEGEND

34950-XXXX

CUSTOMER MODEL COMPONENTS

- 0 - SCHLEMMER BACKSHELL ONLY
- 1 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
- 2 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
- 3 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
- 4 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY D ASSEMBLY
- 5 - MOLEX BACKSHELL ONLY
- 6 - MOLEX BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
- 7 - MOLEX BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
- 8 - MOLEX BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
- 9 - MOLEX BACKSHELL & MX150 HOUSING KEY D ASSEMBLY

BACKSHELL FEATURES

- 1 - WITH RIBS
- 2 - WITHOUT RIBS
- 3 - 90° ADAPTOR

MX150 CIRCUIT SIZE 04, 06, 08, 12, 16, 20

BLADE SEALED ASSEMBLY







BACKSHELL (BKS)

90° ADAPTOR

SCALE 1.5:1

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex						
	mm		1.5:1													
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/01 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16					MX150 GEN 2 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL						
 = 0																
 = 0	ANGULAR TOL		± 3.0 °		INITIAL REVISION: DRWN: KBORUSZEWSKI 2014/02/19 APPR: VKOSHY 2014/03/05					PRODUCT CUSTOMER DRAWING						
 = 0	4 PLACES		±													
 = 0	3 PLACES		±		DOCUMENT NUMBER					DOC TYPE		DOC PART		REVISION		
 = 0	2 PLACES		± 0.1													
 = 0	1 PLACE		± 0.2		SD-160011-0001					PSD		001		A5		
 = 0	0 PLACES		±													
 = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
 = 0							A1-SIZE		160011				GENERAL MARKET		7 OF 11	

SHEET DESCRIPTION	
SCHLEMMER BACKSHELL	









Partial A-A
SCALE 7:2

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex				
	mm		3.5:1											
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/01 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16					MX150 GEN 2 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL				
 = 0														
 = 0	ANGULAR TOL ± 3.0 °				INITIAL REVISION: DRWN: KBORUSZEWSKI 2014/02/19 APPR: VKOSHY 2014/03/05					PRODUCT CUSTOMER DRAWING				
 = 0	4 PLACES ±													
 = 0	3 PLACES ±				DOCUMENT NUMBER SD-160011-0001					DOC TYPE PSD		DOC PART 001		REVISION A5
 = 0	2 PLACES ± 0.1													
 = 0	1 PLACE ± 0.2				THIRD ANGLE PROJECTION					MATERIAL NUMBER A1-SIZE 160011				
 = 0	0 PLACES ±													
 = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				 DRAWING A1-SIZE					CUSTOMER GENERAL MARKET				
 = 0														
 = 0										SHEET NUMBER 8 OF 11				

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:24
-----------------	----	--------------	---------------------

SHEET DESCRIPTION	
MOLEX BACKSHELL	





SECTION B-B

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
	= 0	DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/01 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: KBORUSZEWSKI 2014/02/19 APPR: VKOSHY 2014/03/05				molex MX150 GEN 2 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL							
	= 0	mm		1:1													
	= 0	GENERAL TOLERANCES (UNLESS SPECIFIED)								PRODUCT CUSTOMER DRAWING							
	= 0	ANGULAR TOL		± 3.0 °													
	= 0	4 PLACES		±						DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
	= 0	3 PLACES		±		SD-160011-0001		PSD		001		A5					
	= 0	2 PLACES		± 0.1		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
	= 0	1 PLACE		± 0.2													
	= 0	0 PLACES		±		A1-SIZE		160011		GENERAL MARKET		9 OF 11					
	= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS															
	= 0																

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:24
-----------------	----	--------------	---------------------



MOLEX BACKSHELL CONFIGURATIONS

CHARTED DIMENSIONS												
CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS									
			U	V	W	X	Y	AA	AB	AC	AD	AE
2X4	STANDARD	STANDARD	115.29	94.34	93.98	75.62	32.10	32.93	32.54	32.85	31.76	56.81
2X8	STANDARD	STANDARD	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A
2X10	STANDARD	STANDARD	132.54	102.79	102.78	84.07	36.10	45.44	45.44	42.65	45.44	68.18





(Ø DIM AA)
MIN PASS-THRU
WITH NO CLEARANCE

OVERALL MATED SYSTEM WITH BLADE AND RECEPTACLE BACKSHELL





(Ø DIM AB)
MIN PASS-THRU
WITH NO CLEARANCE

OVERALL MATED SYSTEM WITH BLADE BACKSHELL





(Ø DIM AC)
MIN PASS-THRU
WITH NO CLEARANCE

OVERALL MATED SYSTEM WITH RECEPTACLE BACKSHELL



(Ø DIM AD)
MIN PASS-THRU
WITH NO CLEARANCE

BLADE SEALED ASSEMBLY WITH BLADE BACKSHELL



(Ø DIM AE)
MIN PASS-THRU
WITH NO CLEARANCE

ADD THE VALUE OF 'Y' TO THE TOTAL DIMENSION
WHENEVER ADAPTOR IS USED

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 □ = 0 ■ = 0 ▽ = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex MX150 GEN 2 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL								
	mm		1:1													
	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/01 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16			PRODUCT CUSTOMER DRAWING								
	ANGULAR TOL ± 3.0°															
	4 PLACES ±				INITIAL REVISION: DRWN: KBORUSZEWSKI 2014/02/19 APPR: VKOSHY 2014/03/05			DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION				
	3 PLACES ±							SD-160011-0001		PSD	001	A5				
	2 PLACES ± 0.1															
	1 PLACE ± 0.2				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
	0 PLACES ±															
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						A1-SIZE		160011		GENERAL MARKET		11 OF 11			

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16	22:02:24
-----------------	----	--------------	------------	----------

MX150 GEN 2 BLADE 2X4 SEALED ASSEMBLY MAT SEAL
BOM AND PIN OUT SHEET

CONNECTOR HOUSING
FOR OPTIONS SEE BOM

GROMMET CAP
FOR OPTIONS SEE BOM

MAT SEAL

PRIMARY LOCK REINFORCEMENT
(PLR)

TERMINAL POSITION 4

TERMINAL POSITION 1

TERMINAL POSITION 8

TERMINAL POSITION 5

ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLK-CLIP	HOUSING KEYING OPTION A WITH CLIPSLOT	BLACK	SPS/NYLON GF20
B-LG-CLIP	HOUSING KEYING OPTION B WITH CLIPSLOT	LIGHT GRAY	SPS/NYLON GF20
C-DG-CLIP	HOUSING KEYING OPTION C WITH CLIPSLOT	DARK GRAY	SPS/NYLON GF20
D-SG-CLIP	HOUSING KEYING OPTION D WITH CLIPSLOT	STONE GRAY	SPS/NYLON GF20
GCP	GROMMET CAP (PLUGGED)	BLACK	SPS/NYLON GF20
GCO	GROMMET CAP (OPEN)	BLACK	SPS/NYLON GF20
PLR-1	PLR-1	NATURAL	SPS/NYLON GF20
PLR-3	PLR-3	NATURAL	SPS/NYLON GF20
M-R	MAT SEAL	RUST RED	INHERENTLY LUBRICATED SILICONE
M-B	MAT SEAL	ROYAL BLUE	INHERENTLY LUBRICATED SILICONE

FOR ADDITIONAL INFORMATION SEE SD-160011-0001

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS								STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY			
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION										BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8						
KEY A, BLACK, WITH CLIPSLOT	160011-4001	A-BLK-CLIP	GCO	PLR-1	M-R									PLANNED OBSOLECENCE		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY, WITH CLIPSLOT	160011-4002	B-LG-CLIP	GCO	PLR-1	M-R									PLANNED OBSOLECENCE		34950-0811	34950-0821	34951-0831	34951-0841
KEY C, DARK GRAY, WITH CLIPSLOT	160011-4003	C-DG-CLIP	GCO	PLR-1	M-R									PLANNED OBSOLECENCE		34950-0811	34950-0821	34951-0831	34951-0841
KEY D, STONE GRAY, WITH CLIPSLOT	160011-4004	D-SG-CLIP	GCO	PLR-1	M-R									PLANNED OBSOLECENCE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK, WITH CLIPSLOT	160011-4007	A-BLK-CLIP	GCP	PLR-1	M-R	1	2	3	4	5	6	7	8	PLANNED OBSOLECENCE		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY, WITH CLIPSLOT	160011-4008	B-LG-CLIP	GCP	PLR-1	M-R	1	2	3	4	5	6	7	8	PLANNED OBSOLECENCE		34950-0811	34950-0821	34951-0831	34951-0841
KEY C, DARK GRAY, WITH CLIPSLOT	160011-4009	C-DG-CLIP	GCP	PLR-1	M-R	1	2	3	4	5	6	7	8	PLANNED OBSOLECENCE		34950-0811	34950-0821	34951-0831	34951-0841
KEY D, STONE GRAY, WITH CLIPSLOT	160011-4010	D-SG-CLIP	GCP	PLR-1	M-R	1	2	3	4	5	6	7	8	PLANNED OBSOLECENCE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK, WITH CLIPSLOT	160011-4013	A-BLK-CLIP	GCP	PLR-1	M-R				4	5				PLANNED OBSOLECENCE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK, WITH CLIPSLOT	160011-4014	A-BLK-CLIP	GCP	PLR-1	M-R					5	6		8	PLANNED OBSOLECENCE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK, WITH CLIPSLOT	160011-4015	A-BLK-CLIP	GCP	PLR-1	M-R				4	5			8	SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK, WITH CLIPSLOT	160121-4801	A-BLK-CLIP	GCO	PLR-3	M-B									OK TO TOOL		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY, WITH CLIPSLOT	160121-4802	B-LG-CLIP	GCO	PLR-3	M-B									OK TO TOOL		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK, WITH CLIPSLOT	160121-4811	A-BLK-CLIP	GCP	PLR-3	M-B				4	5				OK TO TOOL		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK, WITH CLIPSLOT	160121-4832	A-BLK-CLIP	GCP	PLR-3	M-B					5	6		8	OK TO TOOL		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK, WITH CLIPSLOT	160121-4834	A-BLK-CLIP	GCP	PLR-3	M-B	1	2	3	4	5	6	7	8	OK TO TOOL		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY, WITH CLIPSLOT	160121-4847	B-LG-CLIP	GCP	PLR-3	M-B	1	2	3	4	5	6	7	8	OK TO TOOL		34950-0811	34950-0821	34951-0831	34951-0841
KEY C, DARK GRAY, WITH CLIPSLOT	160121-4852	C-DG-CLIP	GCO	PLR-3	M-B									OK TO TOOL		34950-0811	34950-0821	34951-0831	34951-0841
KEY D, STONE GRAY, WITH CLIPSLOT	160121-4853	D-SG-CLIP	GCO	PLR-3	M-B									OK TO TOOL		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK, WITH CLIPSLOT	160121-4854	A-BLK-CLIP	GCP	PLR-3	M-B				4	5			8	OK TO TOOL		34950-0811	34950-0821	34951-0831	34951-0841

MX150 GEN 2 BLADE 2X6 SEALED ASSEMBLY MAT SEAL
BOM AND PIN OUT SHEET

ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLK-CLIP	HOUSING KEYING OPTION A WITH CLIPSLOT	BLACK	SPS/NYLON GF20
B-LG-CLIP	HOUSING KEYING OPTION B WITH CLIPSLOT	LIGHT GRAY	SPS/NYLON GF20
C-DG-CLIP	HOUSING KEYING OPTION C WITH CLIPSLOT	DARK GRAY	SPS/NYLON GF20
D-SG-CLIP	HOUSING KEYING OPTION D WITH CLIPSLOT	STONE GRAY	SPS/NYLON GF20
GCP	GROMMET CAP (PLUGGED)	BLACK	SPS/NYLON GF20
PLR-1	PLR-1	NATURAL	SPS/NYLON GF20
PLR-3	PLR-3	NATURAL	SPS/NYLON GF20
M-R	MAT SEAL	RUST RED	INHERENTLY LUBRICATED SILICONE
M-B	MAT SEAL	ROYAL BLUE	INHERENTLY LUBRICATED SILICONE

FOR ADDITIONAL INFORMATION SEE SD-160011-0001

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12				
KEY A, BLACK, WITH CLIPSLOT	160011-6001	A-BLK-CLIP	GCP	PLR-1	M-R													PLANNED OBSOLESCENCE		34950-1210	34950-1220
KEY B, LIGHT GRAY, WITH CLIPSLOT	160011-6002	B-LG-CLIP	GCP	PLR-1	M-R													PLANNED OBSOLESCENCE		34950-1210	34950-1220
KEY C, DARK GRAY, WITH CLIPSLOT	160011-6003	C-DG-CLIP	GCP	PLR-1	M-R													PLANNED OBSOLESCENCE		34950-1210	34950-1220
KEY D, STONE GRAY, WITH CLIPSLOT	160011-6004	D-SG-CLIP	GCP	PLR-1	M-R													PLANNED OBSOLESCENCE		34950-1210	34950-1220
KEY A, BLACK, WITH CLIPSLOT	160011-6007	A-BLK-CLIP	GCP	PLR-1	M-R	1	2	3	4	5	6	7	8	9	10	11	12	PLANNED OBSOLESCENCE		34950-1210	34950-1220
KEY B, LIGHT GRAY, WITH CLIPSLOT	160011-6008	B-LG-CLIP	GCP	PLR-1	M-R	1	2	3	4	5	6	7	8	9	10	11	12	PLANNED OBSOLESCENCE		34950-1210	34950-1220
KEY C, DARK GRAY, WITH CLIPSLOT	160011-6009	C-DG-CLIP	GCP	PLR-1	M-R	1	2	3	4	5	6	7	8	9	10	11	12	PLANNED OBSOLESCENCE		34950-1210	34950-1220
KEY D, STONE GRAY, WITH CLIPSLOT	160011-6010	D-SG-CLIP	GCP	PLR-1	M-R	1	2	3	4	5	6	7	8	9	10	11	12	PLANNED OBSOLESCENSE		34950-1210	34950-1220
KEY A, BLACK, WITH CLIPSLOT	160121-6201	A-BLK-CLIP	GCP	PLR-3	M-B													OK TO TOOL		34950-1210	34950-1220
KEY B, LIGHT GRAY, WITH CLIPSLOT	160121-6202	B-LG-CLIP	GCP	PLR-3	M-B													OK TO TOOL		34950-1210	34950-1220
KEY A, BLACK, WITH CLIPSLOT	160121-6227	A-BLK-CLIP	GCP	PLR-3	M-B	1	2	3	4	5	6	7	8	9	10	11	12	OK TO TOOL		34950-1210	34950-1220
KEY B, LIGHT GRAY, WITH CLIPSLOT	160121-6228	B-LG-CLIP	GCP	PLR-3	M-B	1	2	3	4	5	6	7	8	9	10	11	12	OK TO TOOL		34950-1210	34950-1220
KEY C, DARK GRAY, WITH CLIPSLOT	160121-6261	C-DG-CLIP	GCP	PLR-3	M-B													OK TO TOOL		34950-1210	34950-1220
KEY D, STONE GRAY, WITH CLIPSLOT	160121-6262	D-SG-CLIP	GCP	PLR-3	M-B													OK TO TOOL		34950-1210	34950-1220
KEY C, DARK GRAY, WITH CLIPSLOT	160121-6263	C-DG-CLIP	GCP	PLR-3	M-B	1	2	3	4	5	6	7	8	9	10	11	12	OK TO TOOL		34950-1210	34950-1220
KEY D, STONE GRAY, WITH CLIPSLOT	160121-6264	D-SG-CLIP	GCP	PLR-3	M-B	1	2	3	4	5	6	7	8	9	10	11	12	OK TO TOOL		34950-1210	34950-1220



ECN NO.: 677478	DOCUMENT NO.: SD-160011-0002	REV
DATE:9/22/2021		PAY

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT					BLOCKED TERMINALS																				STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPARATELY			
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.					CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																						BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20							
KEY A, BLACK, WITH CLIPSLOT	160121-2329	A-BLK-CLIP	GCP	PLR-3	M					5	6	7	8			11	12									SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2330	A-BLK-CLIP	GCP	PLR-3	M					5	6	7	8	9	10	11	12	13	14	15						SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2331	A-BLK-CLIP	GCP	PLR-3	M					5	6	7	8													SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2332	A-BLK-CLIP	GCP	PLR-3	M					5	6	7											18	19		SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2333	A-BLK-CLIP	GCP	PLR-3	M					5	6	7				11	12	13	14	15			18	19		SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2334	A-BLK-CLIP	GCP	PLR-3	M	1		3	4	5														19		SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY B, LIGHT GRAY, WITH CLIPSLOT	160121-2335	B-LG-CLIP	GCP	PLR-3	M		2		4															19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2336	A-BLK-CLIP	GCP	PLR-3	M	1	2	3				7	8		10	11						17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2337	A-BLK-CLIP	GCP	PLR-3	M	1							8			11						17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2338	A-BLK-CLIP	GCP	PLR-3	M		2	3				7			10	11						17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2339	A-BLK-CLIP	GCP	PLR-3	M			2				7			10							17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2340	A-BLK-CLIP	GCP	PLR-3	M			3					8			11						17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2341	A-BLK-CLIP	GCP	PLR-3	M	1	2	3			6	7	8		10	11						17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2342	A-BLK-CLIP	GCP	PLR-3	M		2	3			6	7			10	11						17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2343	A-BLK-CLIP	GCP	PLR-3	M		2				6	7			10							17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2344	A-BLK-CLIP	GCP	PLR-3	M						6											17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2345	A-BLK-CLIP	GCP	PLR-3	M	1	2				6	7	8		10							17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2346	A-BLK-CLIP	GCP	PLR-3	M					5	6	7	8	9												SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2347	A-BLK-CLIP	GCP	PLR-3	M		2	3	4	5	6	7	8	9		11		13	14				19	20		SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2348	A-BLK-CLIP	GCP	PLR-3	M				4	5	6	7			9	10	11	12	13	14	15		18	19		SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2349	A-BLK-CLIP	GCP	PLR-3	M				4	5	6	7		9	10	11	12						18	19		SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2350	A-BLK-CLIP	GCP	PLR-3	M					5	6	7				11	12						18	19		SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2351	B-LG-CLIP	GCP	PLR-3	M											11	12	13	14	15	16	17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY B, LIGHT GRAY, WITH CLIPSLOT	160121-2352	B-LG-CLIP	GCP	PLR-3	M		2			5			8			11		13	14	15	16	17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY B, LIGHT GRAY, WITH CLIPSLOT	160121-2353	B-LG-CLIP	GCP	PLR-3	M															15						SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY B, LIGHT GRAY, WITH CLIPSLOT	160121-2354	B-LG-CLIP	GCP	PLR-3	M																16	17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY B, LIGHT GRAY, WITH CLIPSLOT	160121-2355	B-LG-CLIP	GCP	PLR-3	M		2								10	11	12	13		15	16	17	18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2356	A-BLK-CLIP	GCP	PLR-3	M	1	2																18	19	20	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2357	A-BLK-CLIP	GCP	PLR-3	M				4	5	6	7	8	9	10	11	12	13	14	15			18	19		SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2358	A-BLK-CLIP	GCP	PLR-3	M					5	6	7	8			11	12	13	14	15			18	19		SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2359	A-BLK-CLIP	GCP	PLR-3	M				4	5	6	7	8	9	10			13	14	15			18	19		SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2360	A-BLK-CLIP	GCP	PLR-3	M					5	6	7	8					13	14	15				18	19	SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2361	A-BLK-CLIP	GCP	PLR-3	M				4				7	8	9	10	11	12	13	14			18	19		SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2362	A-BLK-CLIP	GCP	PLR-3	M							7	8			11	12	13	14				18	19		SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2363	A-BLK-CLIP	GCP	PLR-3	M				4			7	8	9	10			13	14				18	19		SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK, WITH CLIPSLOT	160121-2364	A-BLK-CLIP	GCP	PLR-3	M							7	8					13	14				18	19		SALEABLE		34950-2011	34950-2021</			

TABLE OF CONTENTS

SHEET NO.	SHEET DESCRIPTION
1	NOTES AND BOM
2	CONFIGURATIONS
3-4	KEY CONFIGURATIONS
5	BLADE SEALED ASSEMBLY
6	SYSTEM PACKAGING
7	BACKSHELL NOTES
8	BACKSHELL
9	BACKSHELL CONFIGURATIONS

2X2

2X3

2X4

2X6

2X8

2X10

INSPECTION NUMBER LOG

LAST NUMBER: 9	
ADDED:	
REMOVED:	

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	CURRENT REV DESC:	molex			
= 0	DIMENSION UNITS	SCALE	EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14			
= 0	mm	1.5:1				
= 0	GENERAL TOLERANCES (UNLESS SPECIFIED)					
= 0	ANGULAR TOL ± 1.0 °					
= 0	4 PLACES ±					
= 0	3 PLACES ±	THIRD ANGLE PROJECTION 				
= 0	2 PLACES ± 0.1					
= 0	1 PLACE ± 0.2					
= 0	0 PLACES ±					
= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING	SERIES	MATERIAL NUMBER	
			A1-SIZE	33482	CUSTOMER	
					GENERAL MARKET	
					SHEET NUMBER	
					1 OF 11	

NOTES: VALID UNLESS OTHERWISE SPECIFIED

1. GENERAL:

a. APPLICATION SPECIFICATION SEE: AS-33472-100

-CONTAINS: PRODUCT INTRODUCTION, PRODUCT SUMMARY, CONNECTOR ASSEMBLY, PACKAGING INFORMATION, CONNECTOR MATING, SERVICE INSTRUCTIONS, ELECTRICAL CONTINUITY CHECKING, CRIMPING, AND TROUBLESHOOTING.

-DESIGNED TO MATE WITH RECEPTACLE SEALED ASSEMBLY AS SPECIFIED IN THE MATING CONNECTOR DRAWINGS CHART.

*DENOTES DRAWINGS THAT CAN BE ACCESSED AT <http://ewcap.uscarteams.org/>.

-ASSEMBLY SHIPPED WITH PLR IN PRE-LOCK POSITION (SEE PLR PRE-LOCK VIEW SHEET 5).

b. PRODUCT SPECIFICATION SEE:

-STANDARD CONFIGURATION: PS-33472-000

-UL V0 CONFIGURATION: TBD

CONTAINS: PRODUCT INTRODUCTION, PRODUCT SUMMARY, RATINGS (CURRENT, TEMPERATURE, SEALING, AND FLAMMABILITY), TERMINALS, WIRE DIAMETER RANGE, PRODUCT VALIDATION, AND PRODUCT DEVIATIONS.

c. PACKAGING SPECIFICATION PER MOLEX DRAWING: PK-31300-635

d. PARTS MUST BE IN COMPLIANCE TO MOLEX CHEMICAL SUBSTANCES FOR PRODUCTS AND PACKAGING SPECIFICATION: QEHS-699000-300

e. DATA MUST BE SUBMITTED UNDER THE MOLEX PART NUMBER TO IMDS (COMPANY ID#13255)

2. DESIGN - MATERIALS:

a. FOR BILL OF MATERIALS SEE:

-STANDARD CONFIGURATION: SD-33482-0002

-UL V0 CONFIGURATION: SD-160084-0002

3. DESIGN - GEOMETRY:

a. THE 3-D CAD DATA IS BASIC (WITHOUT TOLERANCE) AND MASTER FOR THIS PART WITH THE EXCEPTION OF UNDERLINED DIMENSIONS. DIMENSIONAL INFORMATION NOT SHOWN ON THIS DRAWING IS DEFINED BY THE DATA FILE AT ITS LATEST REVISION.

b. GEOMETRIC DIMENSIONS AND TOLERANCES PER ASME Y14.5M-2009

c. EDGES AND UNDIMENSIONED DETAILS PER ISO13715

d. CORNERS SHOWN AS SHARP TO BE R 0.2 MAX.

e. LETTERING SHALL BE 0.15 MAX RAISED IN 0.25 MAX RECESS PAD. THIS INCLUDES RECYCLING CODE, CAVITY ID, VENDOR IDENTIFICATION, AND CUSTOMER MATERIAL NUMBER.

f. VISUAL DEFECTS SHALL MEET COSMETIC STANDARD PS-45499-002 (Class B).

g. LASER MARKING:

1. PART NUMBER

2. DAY OF THE YEAR

3. SHIFT

4. YEAR

FOR ADDITIONAL INFORMATION SEE SECTION 5 UNDER PROCEDURES IN ES-34735-008.

MATING CONNECTOR DRAWINGS

DESCRIPTION	MOLEX INLINE
2X2	SD-33472-0001
2X3	SD-33472-0001
2X4	SD-33472-0001
2X6	SD-33472-0001
2X8	SD-33472-0001
2X10	SD-33472-0001

DOCUMENT STATUS










P1


RELEASE DATE

2018/02/16

22:02:26









SHEET DESCRIPTION	
CONFIGURATIONS	

		
2X2 - STANDARD (STD)	2X2 - UL V0*	
		
2X3 - STANDARD (STD)		2X3 - LENGTHENED
		
2X4 - STANDARD (STD)		
		
2X6 - STANDARD (STD)		
		
2X8 - STANDARD (STD)		
		
2X10 - STANDARD (STD)	2X10 - UL V0*	
DOCUMENT STATUS	P1	RELEASE DATE
		2018/02/16 22:02:26




UL V0 UNIQUE FEATURE
Partial1
SCALE 10:1

* MINOR GEOMETRY CHANGE THAN STANDARD CONFIGURATION.
SEE NOTE 2a FOR MORE INFORMATION


SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																		
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex									
	mm		1.5:1																
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14										MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL				
 = 0																			
 = 0	ANGULAR TOL ± 1.0 °																		
 = 0	4 PLACES ±														PRODUCT CUSTOMER DRAWING				
 = 0	3 PLACES ±																		
 = 0	2 PLACES ± 0.1																		
 = 0	1 PLACE ± 0.2				DOCUMENT NUMBER SD-33482-0001										DOC TYPE	DOC PART	REVISION		
 = 0	0 PLACES ±														PSD	001	E2		
= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER			SHEET NUMBER			
= 0							A1-SIZE		33482				GENERAL MARKET			2 OF 11			

SHEET DESCRIPTION
KEY CONFIGURATIONS CONT.


2X6




KEY A



KEY B




KEY C




KEY D


2X8




KEY A



APPENDIX




1




KEY D


2X10




KEY A



KEY B



KEY C










KFY D

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex					
mm		3:1											
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16				MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL							
ANGULAR TOL ± 1.0 °													
4 PLACES ±		INITIAL REVISION:				PRODUCT CUSTOMER DRAWING							
3 PLACES ±													
2 PLACES ± 0.1		DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14				DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
1 PLACE ± 0.2													
0 PLACES ±		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS													
		A1-SIZE		33482				GENERAL MARKET		4 OF 11			


SHEET DESCRIPTION	
BLADE SEALED ASSEMBLY	

CHARTED DIMENSION					
DESCRIPTION	DIMENSIONS				
	A	B	C	D	E
2X2	15.54	1.75	24.40	54.45	22.23
2X3 STANDARD	19.04	3.50	26.21	54.45	22.23
2X3 LENGTHENED	19.04	3.50	26.21	56.45	22.23
2X4	22.54	1.75	27.21	54.45	22.23
2X6	29.54	1.75	32.27	54.45	22.23
2X8	36.54	1.75	38.88	54.45	22.23
2X10	43.64	1.75	45.65	54.45	22.05



PRIMARY LOCK REINFORCEMENT (PLR) SHOWN IN PRE-STAGED POSITION

SECTION W-W



PRIMARY LOCK REINFORCEMENT (PLR) SHOWN IN FINAL-LOCK POSITION

SECTION V-V

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
	= 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex									
		= 0	mm		3:1														
	= 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650				MX150 BLADE									
	= 0																		
	= 0	ANGULAR TOL ± 1.0 °				DRWN: PMANJUNATHAC 2018/01/03				DUAL ROW SEALED ASSEMBLY MAT SEAL									
	= 0	4 PLACES ±				CHK'D: MVANSLAMBROU 2018/02/16													
	= 0	3 PLACES ±				APPR: MVANSLAMBROU 2018/02/16													
	= 0	2 PLACES ± 0.1				INITIAL REVISION:				PRODUCT CUSTOMER DRAWING									
	= 0	1 PLACE ± 0.2				DRWN: APROFFITT 2014/04/28													
	= 0	0 PLACES ±				APPR: VKOSHY 2014/05/14				DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION			
	= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		SD-33482-0001		PSD		001		E2	
	= 0											MATERIAL NUMBER		CUSTOMER		SHEET NUMBER			
	= 0							A1-SIZE		33482		GENERAL MARKET		5 OF 11					


DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:26
-----------------	----	--------------	---------------------

SHEET DESCRIPTION
BACKSHELL NOTES


BACKSHELL NOTES: VALID UNLESS OTHERWISE SPECIFIED

1. GENERAL:


- a. APPLICATION SPECIFICATION SEE: AS-34951-001
- DESIGNED TO MATE WITH BLADE SEALED ASSEMBLY SPECIFIED IN MOLEX DRAWING SD-33482-0001.
 - SYSTEM TO BE USED WITH WIRE WITHIN DIAMETER RANGE OF 1.2mm TO 2.69mm.
 - COMPONENTS ARE OPTIONAL AND MUST BE PURCHASED SEPERATELY.
 - DESIGN IS OWNED BY SCHLEMMER FOR SCHLEMMER BACKSHELL.
 - DESIGN IS OWNED BY MOLEX FOR MOLEX BACKSHELL.
 - 90° ADAPTOR DESIGN IS OWNED BY MOLEX.
 - FOR ADDITIONAL INFORMATION SEE THE BACKSHELL COMPONENT DRAWING SD-34950-0001.




2X3




2X4




2X4



2X6



2X8



2X10

BACKSHELL CUSTOMER
MODEL NUMBER LEGEND

34950-XXXX


CUSTOMER MODEL COMPONENTS

- 0 - SCHLEMMER BACKSHELL ONLY
- 1 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
- 2 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
- 3 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
- 4 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY D ASSEMBLY
- 5 - MOLEX BACKSHELL ONLY
- 6 - MOLEX BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
- 7 - MOLEX BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
- 8 - MOLEX BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
- 9 - MOLEX BACKSHELL & MX150 HOUSING KEY D ASSEMBLY

BACKSHELL FEATURES

- 1 - WITH RIBS
- 2 - WITHOUT RIBS
- 3 - 90° ADAPTOR

MX150 CIRCUIT SIZE 04, 06, 08, 12, 16, 20




90° ADAPTOR

BACKSHELL (BKS)






BLADE SEALED ASSEMBLY

SCALE 1.5:1


SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
	DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14			molex					
	mm		1.5:1										
	GENERAL TOLERANCES (UNLESS SPECIFIED)							MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL					
	ANGULAR TOL ± 1.0 °												
	4 PLACES		±					PRODUCT CUSTOMER DRAWING					
	3 PLACES		±										
	2 PLACES		± 0.1					DOCUMENT NUMBER SD-33482-0001			DOC TYPE	DOC PART	REVISION
	1 PLACE		± 0.2								PSD	001	E2
	0 PLACES		±					MATERIAL NUMBER CUSTOMER GENERAL MARKET			SHEET NUMBER 7 OF 11		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS												
THIRD ANGLE PROJECTION				DRAWING		SERIES							
				A1-SIZE		33482							


DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:26
-----------------	----	--------------	---------------------

SHEET DESCRIPTION	
SCHLEMMER BACKSHELL	




SECTION A-A



SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex			
	mm		3.5:1										
	GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16					MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL					
	ANGULAR TOL ± 1.0 °												
	4 PLACES ±												
	3 PLACES ±		INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14					PRODUCT CUSTOMER DRAWING					
	2 PLACES ± 0.1												
	1 PLACE ± 0.2							DOCUMENT NUMBER		DOC TYPE		DOC PART	
	0 PLACES ±		SD-33482-0001		PSD		001		E2				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
				A1-SIZE		33482				GENERAL MARKET		8 OF 11	

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:26
-----------------	----	--------------	---------------------



SHEET DESCRIPTION	
MOLEX BACKSHELL	

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:26
-----------------	----	--------------	---------------------

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
	= 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex					
	= 0	mm		3:1											
	= 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650				MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL					
	= 0														
	= 0	ANGULAR TOL ± 1.0 °				DRWN: PMANJUNATHAC 2018/01/03				PRODUCT CUSTOMER DRAWING					
	= 0	4 PLACES ±				CHK'D: MVANSLAMBROU 2018/02/16									
	= 0	3 PLACES ±				APPR: MVANSLAMBROU 2018/02/16									
	= 0	2 PLACES ± 0.1				INITIAL REVISION:				DOCUMENT NUMBER SD-33482-0001					
	= 0	1 PLACE ± 0.2				DRWN: APROFFITT 2014/04/28								DOC TYPE PSD	
	= 0	0 PLACES ±				APPR: VKOSHY 2014/05/14				MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
	= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		GENERAL MARKET 9 OF 11			
	= 0							A1-SIZE		33482					

molex

MX150 BLADE
DUAL ROW SEALED ASSEMBLY MAT SEAL


PRODUCT CUSTOMER DRAWING

SD-33482-0001



PSD 001 E2

GENERAL MARKET 9 OF 11



SHEET DESCRIPTION	
SCHLEMMER BACKSHELL CONFIGURATIONS	





OVERALL MATED SYSTEM WITH BLADE AND RECEPTACLE BACKSHELL




OVERALL MATED SYSTEM WITH BLADE BACKSHELL



OVERALL MATED SYSTEM WITH RECEPTACLE BACKSHELL




BLADE SEALED ASSEMBLY WITH BLADE BACKSHELL




CHARTED DIMENSIONS							
CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS				
			M	N	P	R	T
2X3	STANDARD	STANDARD	106.83	32.75	31.75	29.00	29.50
	LENGTHENED		108.71				
2X4	STANDARD	STANDARD	106.83	33.50	31.90	30.70	30.70
2X6	STANDARD	STANDARD	106.83	37.84	37.27	35.83	36.83

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16	22:02:26
-----------------	----	--------------	------------	----------


SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
		DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex					
	= 0	mm		2:1		EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14					MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL					
	= 0	GENERAL TOLERANCES (UNLESS SPECIFIED)														
	= 0	ANGULAR TOL ± 1.0 °									PRODUCT CUSTOMER DRAWING					
	= 0	4 PLACES		±												DOCUMENT NUMBER SD-33482-0001
	= 0	3 PLACES		±							DOC TYPE PSD		DOC PART 001		REVISION E2	
	= 0	2 PLACES		± 0.1		THIRD ANGLE PROJECTION 					MATERIAL NUMBER		CUSTOMER GENERAL MARKET		SHEET NUMBER 10 OF 11	
	= 0	1 PLACE		± 0.2												
	= 0	0 PLACES		±		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										
	= 0															




OVERALL MATED SYSTEM WITH BLADE AND RECEPTACLE BACKSHELL




(Ø DIM AA)
MIN PASS-THRU
WITH NO CLEARANCE




OVERALL MATED SYSTEM WITH BLADE BACKSHELL




(Ø DIM AB)
MIN PASS-THRU
WITH NO CLEARANCE




OVERALL MATED SYSTEM WITH RECEPTACLE BACKSHELL




(Ø DIM AC)
MIN PASS-THRU
WITH NO CLEARANCE




BLADE SEALED ASSEMBLY WITH BLADE BACKSHELL



(Ø DIM AD)
MIN PASS-THRU
WITH NO CLEARANCE



ADD THE VALUE OF 'Y' TO THE TOTAL DIMENSION
WHENEVER ADAPTOR IS USED




(Ø DIM AE)
MIN PASS-THRU
WITH NO CLEARANCE

CHARTED DIMENSIONS


CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS									
			U	V	W	X	Y	AA	AB	AC	AD	AE
2X4	STANDARD	STANDARD	115.24	94.36	93.93	75.62	32.10	32.93	32.54	32.85	31.76	56.81
2X8	STANDARD	STANDARD	132.49	102.81	102.73	84.07	36.10	45.44	45.44	42.65	45.44	68.18
2X10	STANDARD	STANDARD	132.49	102.81	102.73	84.07	36.10	45.44	45.44	42.65	45.44	68.18

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																					
	= 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex													
		mm		1:1																			
	= 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16				MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL													
	= 0																						
	= 0																						
	= 0																						
	= 0																						
	= 0	ANGULAR TOL ± 1.0 °				INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14				PRODUCT CUSTOMER DRAWING													
	= 0	4 PLACES		±										DOCUMENT NUMBER				DOC TYPE		DOC PART		REVISION	
	= 0	3 PLACES		±										SD-33482-0001				PSD		001		E2	
	= 0	2 PLACES		± 0.1																			
	= 0	1 PLACE		± 0.2																			
	= 0	0 PLACES		±		THIRD ANGLE PROJECTION				MATERIAL NUMBER		CUSTOMER		SHEET NUMBER									
	= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS														DRAWING		SERIES					
	= 0															A1-SIZE		33482					
	= 0							A1-SIZE		33482		GENERAL MARKET		11 OF 11									
	= 0																						







SHEET DESCRIPTION	
MOLEX BACKSHELL DETAIL	




98 99
DIM. R ±0.15
ALL AROUND



CHARTED DIMENSION							
DESCRIPTION	DIMENSION						
	H	J	K	L	M	S	R
2X4, WITH RIB	53.56	16.10	0.80	N/A	N/A	16.10	1.35
2X4, WITHOUT RIB	53.56	16.10	N/A	3.60	5.10	16.10	N/A
2X8, WITH RIB	62.01	19.30	0.80	N/A	N/A	19.30	1.45
2X8, WITHOUT RIB	62.01	19.30	N/A	3.60	5.10	19.30	N/A
2X10, WITH RIB	62.01	19.30	0.80	N/A	N/A	19.30	1.45
2X10, WITHOUT RIB	62.01	19.30	N/A	3.60	5.10	19.30	N/A



PARTIAL SECTION C-C
SCALE 5:1
WITH RIBS



PARTIAL SECTION D-D
SCALE 5:1
WITHOUT RIBS

QUALITY SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
FA = 0 FE = 0 FP = 0 ▼ = 0 C = 0 ☒ = 0 ■ = 0 ✓ = 0	EC NO: 638031 DRWN: PPALLAN CHKD: MYANSLAMBROU APPR: MYANSLAMBROU REV: B11	2020/05/20 2020/05/22 2020/05/22	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex® MX150 DUAL ROW BLADE BACKSHELLS PRODUCT CUSTOMER DRAWING		
			ANGULAR TOL ± 3.0 °		mm		2:1				
			4 PLACES ±		DRWN BY		DATE				
			3 PLACES ±		DAHALL		2013/03/19		SERIES 34950 MATERIAL NUMBER SD-34950-0001 CUSTOMER GENERAL MARKET DOCUMENT NUMBER SD-34950-0001 DOC TYPE PSD DOC PART 001 SHEET NUMBER 4 OF 4		
			2 PLACES ± 0.1		CHK'D BY		DATE				
			1 PLACE ± 0.2		APPR BY		DATE				
			0 PLACES ±		VKOSHY		2013/04/08				
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE		THIRD ANGLE PROJECTION				
					A1						