



1					2			3			4		
	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		
△						△					. .		
△						△					. .		
△						△					. .		



NOTE 1 ROTATION EXAMPLES OF REF.NO. 1 AND 8 ARE SHOWN.
2 THE RECOMMENDED TORQUE OF REF.NO. 8: 2 TO 3N · m.
3 THE RECOMMENDED TORQUE OF REF.NO. 11: 0.3 TO 0.4N · m.

			11	STEEL	NICKEL PLATING	THE WIDTH ACROSS OF A HEXAGON SOCKET: 1.27			
			10	BRASS	NICKEL PLATING				
			9	ZINC ALLOY	MATTE FINISH NICKEL PLATING				
			8	ZINC ALLOY	MATTE FINISH NICKEL PLATING				
			7	BRASS	NICKEL PLATING				
			6	BERYLLIUM COPPER	NICKEL PLATING				
			5	BRASS	MATTE FINISH NICKEL PLATING				
4	DIALYL PHTHALATE	(BLACK) UL94V-0							
3	DIALYL PHTHALATE	(BLACK) UL94V-0							
2	COPPER ALLOY	SILVER PLATING 2μm min							
1	ZINC ALLOY	MATTE FINISH NICKEL PLATING							
NO. MATERIAL		FINISH, REMARKS		NO. MATERIAL		FINISH, REMARKS			
CODE NO. (OLD)			DRAWN		DESIGNED		CHECKED	APPROVED	RELEASED
CL									
			T. Suzuki '21.06.03		T. Suzuki '21.06.03		W. Kobayashi '21.06.07	T. Konatsu '21.06.09	
			DRAWING NO.			PART NO.			
SCALE 2 : 1			EDC4-112321-76-00			RM12BPE-4PH(76)			
UNITS mm			HRS HIROSE ELECTRIC CO., LTD.			CODE NO.			1/1
						CL109-0419-2-76			