


1					2					3					4				
COUNT	DESCRIPTION OF REVISIONS				BY	CHKD	DATE			COUNT	DESCRIPTION OF REVISIONS				BY	CHKD	DATE		
△										△									
△										△									
△										△									



- NOTES
- 1 THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑩ TO BE 0.2 TO 0.3 N·m. LOCTITE 242, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. ⑩ FROM LOOSENING.
 - 2 ROTATION EXAMPLES OF REF. NO. ① AND ⑥ ARE SHOWN.
 - 3 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE. PLEASE CONFIRM BEFORE THE USE.

10	BRASS	NICKEL PLATING	9	PHOSPHOR BRONZE	NICKEL PLATING
8	BRASS	NICKEL PLATING	7	BRASS	NICKEL PLATING
6	BRASS	NICKEL PLATING	5	BRASS	NICKEL PLATING
2	COPPER ALLOY	SILVER PLATING 2μm min.	4	DIALLYL PHTHALATE	(BLACK) UL94V-0
1	BRASS	NICKEL PLATING	3	DIALLYL PHTHALATE	(BLACK) UL94V-0
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS

CODE NO. (OLD)	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
	T. Suzuki	T. Suzuki	H. Kobayashi	T. Kawanishi	
	21.06.03	21.06.03	21.06.07	21.06.09	

DRAWING NO.	PART NO.
EDC4-028098-76-00	RM15TP-10PH(76)
CODE NO.	
CL109-0857-0-76	

TO
R

SCALE	2 : 1
UNITS	mm

HRS

HIROSE ELECTRIC CO., LTD.