
Pro-SIGNAL	PART NO.		REVISIONS									
	ABI-007-RC	ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE		
		-	А	RELEASED	Jagan	06/04/09	Veena	06/04/09	Farnell	20/04/09		





Tolerance: ±0.5

Dimensions : Millimetres

DRAWN BY:

Farnell

All data at 25°C unless otherwise specified.

Specifications	ABI-007-RC Piezo Indicator			
Rated Voltage	12V dc			
Operating Voltage	3 to 16V dc			
Rated Current at Rated Voltage	8mA			
Sound Output at 30cm, at Rated Voltage	≥90dB			
Resonant Frequency at Rated Voltage	3700 ±500Hz			
Operating Temperature	-20 to +60°C			
Storage Temperature	-30 to +80°C			
Weight	5g			

TOLERANCES:

SPECIFIED,

UNLESS OTHERWISE

DIMENSIONS ARE

FOR REFERENCE

PURPOSES ONLY.

Part Number Table

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for

(the restorp) or are noted to it to vilcence the products to which it relates. No licence information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change with out notice and replaces all data sheets previously supplied. The Information supplied is

believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this

data sheet should check for themselves the Information and the suitability of the prod-

ucts for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or

United, Lability including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC pro-SIGNAL is the registered trademark of the Group. © Premier Famel pic 2009.

Description	Part Number				
Piezo Buzzer, 12V dc, PCB	ABI-007-RC				

ABI-007-RC - Piezo Buzzer 06/04/09 Jagan CHECKED BY: DATE: ELECTRONIC FILE SIZE DWG NO. 06/04/09 Veena 66692_DWG А APPROVED BY: DATE: SHEET: 1 OF 1 SCALE: NTS U.O.M.: mm 20/04/09

DRAWING TITLE:

DATE:

Features:

- Colour : Black.
- Housing material : Noryl. ٠
- Sealed base. •
- Wave solderable and washable.

http://www.farnell.com

http://www.newark.com

REV

А

http://www.cpc.co.uk