


REVISIONS								
REV	ECO	DESCRIPTION	DATE	BY	APPR			
A1		RELEASE NEW DRAWING	12MAY20	IAN	TOMMY			
A2		MODIFY PRODUCT NAME	11AUG20	IAN	TOMMY			



NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:


HOUSING: THERMOPLASTIC; BLACK SEAL: SILICONE RUBBER

2. MODIFICATIONS: SMOOTH RING ADAPTER (SRA); REDUCED DIA. WIRE SEAL;

- 3. SPECIFICATIONS:
  - 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
  - 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
  - 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
  - 3.4 MOISTURE RESISTANCE: IP67&IP69K (MATED CONDITION).
  - 3.5 MATING CYCLE DURABILITY: 100 CYCLES
  - 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP06-24-31P\* (\* = SEAL TYPE)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
- 6 CONTACT SIZE AND WIRE RANGE:


CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL WIRE	CURRENT
SIZE	O.D.	O.D.	RANGE	RATING
16	1.35 mm (.053in)	2.62 mm ( .103in)	14-20 AWG (2.0-0.5mm²)	13 AMPS

7. RECEPTACLE IS SUPPLIED WITH DUST CAP.



RECOMMENDED PANEL MOUNTING HOLE

RECOMMENDED PANEL THICKNESS:1.6 TO 4.7MM



	AHDP04-24-31SR-SRA			REF:HDP24-24-31SE		
	PART NUMBER			DESCRIPTION		
QUANTITY			MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED.  ) All dimensions are in metricum. 2) Tolerances are as follows: 1PL DEC a) 15 3PL DEC a) 0.5 3PL DEC a) 0.5 3Note reference =   MATERIAL SPECIFICATIONS:		SIGI	NATURES	DATE	Amphonol	
		DRAWN:	IAN.XIAO	11AUG20	<ul><li>Amphenol</li></ul>	
		CHECKED:	ORION.LI	12AUG20	Sine Systems - www.amphenol-sine.com	
		ENGINEER:			44724 Morley Drive Clinton Township, MI 48036	
		APPROVAL:	TOMMY.XIE	13AUG20	Clinton Township, Wi 48030	
		CUSTOMER:			RECEPT,SIZE 24,31-SOCKET,	
			NG IS SUPPLIED		RD01 SEAL,SRA,DURAMATE AHDP SEIRES	
PROCESS SPECIFICA	HONS:			ODMANIOT DATA	I I I I	

SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

NEXT ASS'Y

B C-

SCALE: NONE

DURAMATE SHEET 1 OF 1

## **AT Series™** - Contact Size 16 Options

Machined Contacts, Sockets & Pins							
Part Number	Description		AWG	Туре			
AT60-215-1631	Male Contact - Pin, Gold-plated	16	14	Machined			
AT62-209-1631	Female Contact - Socket, Gold-plated	16	14	Machined			
AT60-215-16141	Male Contact - Pin, Nickel-plated	16	14	Machined			
AT62-209-16141	Female Contact - Socket, Nickel-plated	16	14	Machined			
AT60-202-1631	Male Contact - Pin, Gold-plated	16	16-20	Machined			
AT62-201-1631	Female Contact - Socket, Gold-plated	16	16-20	Machined			
AT60-202-16141	Male Contact - Pin, Nickel-plated 16		16-20	Machined			
AT62-201-16141	Female Contact - Socket, Nickel-plated	16	16-20	Machined			
AT60-202-1631-22	Male Contact - Pin, Gold-plated	16	22-24	Machined			
AT62-201-1631-22	1-22 Female Contact - Socket, Gold-plated		22-24	Machined			
AT60-202-16141-22	Male Contact - Pin, Nickel-plated	16	22-24	Machined			
AT62-201-16141-22	Female Contact - Socket, Nickel-plated	16	22-24	Machined			

Tooling - Machined Contacts					
Part	Part Number	Part Number Description			
	CA-5D12	Universal Hand Crimp Tool, Size 12/16/20 (Machined contacts only)			
3	CA-5E12	Pneumatic Crimp Tool, Size 12/16/20 (Machined contacts only)			

Contact Removal Tools					
Part	Part Number	Description			
	ATRT-100	Used for removal of contacts for A Series™ products			
	AT11-310-1605	Contact Removal Tool, Plastic, Size 16			
	A114017	Sealing Plug, Size 16, White			

Stamped & Formed Contacts, Sockets & Pins							
Part Number	Description	Size	AWG	Type			
AT60-14-0144	Male Contact - Pin, Gold-plated	16	14-16	Stamped & Formed			
AT62-14-0144	Female Contact - Socket, Gold-plated	16	14-16	Stamped & Formed			
AT60-14-0122	Male Contact - Pin, Nickel-plated	16	14-16	Stamped & Formed			
AT62-14-0122	Female Contact - Socket, Nickel-plated	16	14-16	Stamped & Formed			
AT60-16-0144	Male Contact - Pin, Gold-plated	16	16-18	Stamped & Formed			
AT62-16-0144	Female Contact - Socket, Gold-plated	16	16-18	Stamped & Formed			
AT60-16-0122	Male Contact - Pin, Nickel-plated	16	16-18	Stamped & Formed			
AT62-16-0122	Female Contact - Socket, Nickel-plated	16	16-18	Stamped & Formed			
AT60-16-0644	Male Contact - Pin, Gold-plated	16	18-20	Stamped & Formed			
AT62-16-0644	Female Contact - Socket, Gold-plated	16	18-20	Stamped & Formed			
AT60-16-0622	Male Contact - Pin, Nickel-plated	16	18-20	Stamped & Formed			
AT62-16-0622	Female Contact - Socket, Nickel-plated	16	18-20	Stamped & Formed			
AT60-16-0844	Male Contact - Pin, Gold-plated	16	20-22	Stamped & Formed			
AT62-16-0844	Female Contact - Socket, Gold-plated	16	20-22	Stamped & Formed			
AT60-16-0822	Male Contact - Pin, Nickel-plated	16	20-22	Stamped & Formed			
AT62-16-0822	Female Contact - Socket, Nickel-plated	16	20-22	Stamped & Formed			

Tooling - Stamped & Formed Contacts					
Part	Part Number Description				
	MFX-3950	Crimp Die - Size 16, 18-20AWG (S&F contacts only)			
	MFX-3953	Crimp Die - Size 16, 16-18AWG (S&F contacts only)			
	MFX-3975	Crimp Die - Size 16, 14-16AWG (S&F contacts only)			
	MFX-3990	Crimp Die - Size 16, 20-22AWG (S&F contacts only)			
	ATT-16-00	Hand Crimp Tool - Size 16, 14-16AWG (S&F contacts only)			
	ATT-16-01	Hand Crimp Tool - Size 16, 18-20AWG (S&F contacts only)			
	ATT-1612-03	Hand Crimp Tool - Size 16, 20-22AWG (S&F contacts only)			

Amphenol Sine Systems 44724 Morley Drive Clinton Township, MI 48036 USA www.amphenol-sine.com 09/2021