

10	9	8	7	6	5	4	3	2	1
ITEM	MOLEX P/N	DESCRIPTION	QTY	UOM					
A,B	39014021	MiniFit Jr SR Recpt Hsg 2 CKT V-0	2	PC					
C	39000077	MiniFit Term Crp Fem Chn Bs Tin 16awg	4	PC					
D	--	RESIN TPE NAT SANTOPRENE	A/R	KG					
E	--	MOLD PART INNER CAP	4	PC					
F	--	MASTER BATCH BLACK COLOR	A/R	KG					

FROM	TO	CABLE DESCRIPTION	COLOR
A1	B1	2CX16AWG UNSHD BK UL2464	BLACK
A2	B2		RED




TABLE		
PART NUMBER	TITLE	L1
2153300205	2 CKT OVERMOLDED MINIFIT JR CABLE 500MM	500±10
2153300210	2 CKT OVERMOLDED MINIFIT JR CABLE 1M	1000±20
2153300220	2 CKT OVERMOLDED MINIFIT JR CABLE 2M	2000±25
2153300230	2 CKT OVERMOLDED MINIFIT JR CABLE 3M	3000±30

NOTES:									
1. MOLDING MATERIAL:									
1.1 INNERCAP: PA66 NYLON RESIN.									
1.2 OVERMOLD: SANTOPRENE TPE RESIN & MASTER BATCH BLACK									
2. ELECTRICAL PERFORMANCE:									
2.1 VOLTAGE RATING: 300V AC.									
2.2 THIS PRODUCT MUST PASS 100% CONTINUITY TEST PER MOLEX ES-36586-004.									
1) DIELECTRONIC STRENGTH: 500V DC/0.01 SEC.									
2) INSULATION RESISTANCE: 20M OHMS									
3. CONNECTOR VIEWS ARE SHOWN FROM MATING SIDE.									
4. MECHANICAL PERFORMANCE:									
4.1 CABLE HARNESS SHOULD WITHSTAND AN AXIAL FORCE OF 5KGF FOR ONE MINUTE BETWEEN OVERMOLD AND CONNECTOR WITHOUT PHYSICAL DAMAGE.									
4.2 OVERMOLD SIDE CAN PASS THE BENDING TEST IN 100 CYCLES AT EACH OF 2 PLANES, PER EIA364-41 CONDITION I.									
DOCUMENT STATUS	P1	RELEASE DATE	2021/05/10	17:54:26					

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
SCALE	DIMENSION UNITS	SCALE
$\sqrt{A} = 0$	mm	NTS
$\sqrt{E} = 0$	GENERAL TOLERANCES (UNLESS SPECIFIED)	
$\sqrt{E} = 0$	ANGULAR TOL	± °
$\sqrt{E} = 0$	4 PLACES	±
$\sqrt{E} = 0$	3 PLACES	±
$\sqrt{E} = 0$	2 PLACES	±
$\sqrt{E} = 0$	1 PLACE	±
$\sqrt{E} = 0$	0 PLACES	±
DIVISIONAL SYMBOLS	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION
		DRAWING
		SERIES
		MATERIAL NUMBER
		CUSTOMER
		SHEET NUMBER

EC NO: 662617	2021/05/02
DRWN: SBS04	2021/05/10
CHK'D: MNARAYAN01	2021/05/10
APPR: MNARAYAN01	2021/05/10
INITIAL REVISION:	
DRWN: SBS04	2021/05/01
APPR: MNARAYAN01	2021/05/10

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
2153300205	PSD	000	B

SEE TABLE	GENERAL MARKET	1 OF 1
-----------	----------------	--------