





ELV, RoHS COMPLIANT



PIN ASSIGNMENT

16 32 15 31 14 30 13 29 12 28 11 27 10 26 9 25 8 24 7 23 6 22 5 21 4 20 3 19 2 18 1 17



RECOMMENDED PCB PATTERN

NOTE 1 RECOMMENDED TEMPERATURE PROFILE FOR REFLOW
(REFER TO RIGHT FIG.)
USED REFLOW SYSTEM


NO. OF CYCLES : 2 MAX
PEAK : 250°C
OVER 230°C : 20~40s
PREHEAT : 150~180°C
60~120s

2 TEMPERATURE FOR SOLDERING IRON
280~300°C WITHIN 2s

3 CO-PLANARITY OF PIN SHALL BE 0.1mm MAX.

4 RECOMMENDED PCB THICKNESS IS 1.6mm.

5 RECOMMENDED SOLDER THICKNESS IS 0.15mm.



3	BRASS	TIN PLATED	6	PET	
2	BRASS	TIN PLATED	5	PS	
1	PA	BLACK	4	BRASS	TIN PLATED
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-T-00006626	DESIGNED DONGCHAN KIM
APPROVED : AR. SHIRAI	20180530	DRAWING NO. EDC-361159-10-00	CHECKED : HS. OZAWA	20180530	PART NO. GT25H2-32DP-2. 2H<10>
DESIGNED : YT. HAYAKAWA	20180530	CODE NO. CL775-0086-6-10	DRAWN : DS. HIROWATARI	20180529	

HIROSE

HIROSE
ELECTRIC
CO., LTD.

Mar.1.2022 Copyright 2022 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

