







Mar.1.2022 Copyright 2022 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

ELV, RoHS COMPLIANT




- NOTE1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW
(REFER TO RIGHT FIG.)
USED REFLOW SYSTEM : IR IN THE AIR OR NITROGEN
NO. OF CYCLES : 2 MAX
PEAK : 250°C
OVER 230°C : 20~40s
PREHEAT : 150~180°C 60~120s
2. TEMPERATURE FOR SOLDERING IRON : 280~300°C WITHIN 2s
3. COPLANARITY SHALL BE 0.1mm MAX.
4. RECOMMENDED PCB THICKNESS IS 1.6mm
5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.




3	BRASS	TIN PLATED	6	PET	
2	BRASS	TIN PLATED	5	PS	
1	PA	BLACK	4	BRASS	TIN PLATED
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-T-00006626	DESIGNED DONGCHAN KIM
HIROSE ELECTRIC CO., LTD.		APPROVED : AR. SHIRAI	20180601	DRAWING NO.	EDC-169254-10-00
		CHECKED : HS. OZAWA	20180601	PART NO.	GT25H2-8DP-2. 2H(10)
		DESIGNED : YT. HAYAKAWA	20180601	CODE NO.	CL775-0047-4-10
		DRAWN : YT. HAYAKAWA	20180601		
					DATE 20200902


PACKAGING SPECIFICATION



 REEL DIMENSION (FREE)



CARDBOARD DIMENSION(FREE)



BOX SIZE

$$W = (405) \text{ (mm)}$$
$$D = (405) \text{ (mm)}$$
$$H = (39) \quad (\text{mm})$$

	DRAWING NO.	EDC-169254-10-00	
	PART NO.	GT25H2-8DP-2. 2H<10>	
	CODE NO.	CL775-0047-4-10	 