






- NOTES:
- 1 MATERIALS:
HOUSING - THERMOPLASTIC, BLACK
TERMINALS - COPPER ALLOY, GOLD PLATED
 - 2. SUPPLIED ON TAPE AND REEL, SEE SHEET 2.
 - 3. THIS PRODUCT IS RoHS COMPLIANT.



SCHEMATIC

**PCB LAYOUT
COMPONENT SIDE**

A	28463	01/31/22	PC	TJK
REV	ECO NUMBER	DATE	BY	APVD
REVISIONS				


UNLESS OTHERWISE SPECIFIED				
1. ALL DIMENSIONS IN INCHES [mm]				
- TWO PLACE DECIMALS ±0.02 [0.5]				
- THREE PLACE DECIMALS ±0.005 [0.13]				
A	28463	01/31/22	PC	TJK
REV	ECO NUMBER	DATE	BY	APVD
DO NOT SCALE DRAWING				

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
SIZE		WIDTH		MULT		LBS/M		TEMPER	
FINISH SPEC No.					MATERIAL SPEC No.				
FIRST USED ON				SCALE 6:1		Switchcraft®			
DATE DRAWN	BY	CHKD		APVD					
1/26/22	PC	TJK		TJK					
		1/26/22		1/26/22		SHEET 1 OF 2			
NAME 3.5 MM PHONE JACK SURFACE MOUNT, RoHS					PART No. 35RASMT2BHSNTRX				REV A

CUSTOMER DRAWING


A: CARRIER SIZE

1. DETAIL SIZE REFERENCES: EIA-481
2. SPECIFICATIONS: 24 MM X 16 MM



B: REEL SIZE

1. QUANTITY: 900 PCS/REEL
2. MATERIAL: THERMOPLASTIC



- A: EMPTY 6.30 [160.0] MIN.
- B: EMPTY 3.94 [100.0] MIN.
- C: COVER 15.75 [400.0] MIN.

CUSTOMER DRAWING

SCALE 2:1	Switchcraft®		
DATE DRAWN 1/26/22			
DRAWN BY PC	PART No. 35RASMT2BHSNTRX	REV A	