






RECOMMENDED TORQUE
VALUES:1.9-2.2 N.m

6 CONTACT SIZE AND WIRE RANGE:

CONTACT SIZE	MIN. INSUL O.D.	MAX. INSUL O.D.	TYPICAL WIRE RANGE	CURRENT RATING
4	6.63 mm (.261in)	7.41mm (.292 in)	6 AWG (16-13mm ²)	100 AMPS

RECOMMENDED PANEL THICKNESS:1.6 TO 4.7MM



HDP02-18-06SN-BRAC030		PART NUMBER		DESCRIPTION		ITEM	
MATERIALS LIST							
SE SPECIFIED in metric(mm). follows: Fractions 1/8" Angles 1°		SIGNATURES DRAWN: VITOLI CHECKED: SULLENZWANG ENGINEER: APPROVAL: TOMMY XIE CUSTOMER:		DATE 28MAR22 29MAR22 30MAR22		Amphenol Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036	
A : 52.7g		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION OR TRANSMISSION IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEMS, ARE PERMITTED WITHOUT THE WRITTEN PERMISSION OF AMPHENOL CORPORATION. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.		2POS, RECEPT, SOCKET, PANELMATE AHDP SIZE 18, NORMAL SEAL, BRA, C030		DWG NO.	
B SCALE: NONE		C-		HDP02-18-06SN-BRAC030		REVISION A1	
		DHDURAMATE		SHEET 1 OF 1			

REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	--	RELEASE NEW DRAWING	28MAR22	VITO	TOMMY

