

NOTES: UNLESS OTHERWISE SPECIFIED

MATERIAL:

HOUSING: THERMOPLASTIC: BLACK

SEAL: SILICONE RUBBER

2. MODIFICATIONS: BACKSHELL RING ADAPTER (BRA); REDUCED DIA. WIRE SEAL:

- 3. SPECIFICATIONS:
 - 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
 - 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
 - 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
 - 3.4 MOISTURE RESISTANCE:

IP68(IM OF WATER FOR A PERIOD OF 24 HOURS.MATED CONDITION);


IP69K (MATED CONDITION)

- 3.5 MATING CYCLE DURABILITY: 100 CYCLES
- 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP06-24-31S* (* = SEAL TYPE)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.


6 CONTACT SIZE AND WIRE RANGE:


CONTACT SIZE	MIN. INSUL O.D.	_	TYPICAL WIRE RANGE	CURRENT RATING
16	1.35 mm (.053in)	2.62 mm (.103in)	14-20 AWG (2.0-0.5mm²)	13 AMPS

7. RECEPTACLE IS SUPPLIED WITH DUST CAP.




REVISIONS										
REV	ECO	DESCRIPTION	DATE	BY	APPR					
A1	-	RELEASE NEW DRAWING	01/MAR/22	VITO	TOMMY					
Ø50.8										





RECOMMENDED PANEL MOUNTING HOLE

RECOMMENDED PANEL THICKNESS:1.6 TO 4.7MM



	AHDP04-24-31PR-BRA			REF:HDP24-24-31PE-L017				
QUANTITY PART N		IUMBER		DESCRIPTION		ITEM		
		MA	TEF	TERIALS LIST				
UNLESS OTHER		SIGNATUR	ES DA	Amphor				
2) Tolerandose are as rollows: 1 PL DEC ±0.30 2 PL DEC ±0.16 3 PL DEC ±0.18 3) Note reference = X MATERIAL SPECIFICATIONS:		DRAWN: VITO.LI	01/M	AR/22	Amphenol			
		CHECKED: SULLENZH	NG 02/M/	AR/22	Sine Systems - www.amphenol-sine.com			
		ENGINEER:			44724 Morley Drive			
		APPROVAL: TOMMY.X	E 03/M/	AR/22	Clinton Township, MI 48036			
		CUSTOMER:			31POS, RECEPTACLE, PIN,			
		SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL		es	SIZE 24, RD SEAL, BRA, DURAMATE AHDP			
				DATA OF RIGHTS	B C - AHDP04-24-31PR-BRA A	41		
					SCALE: NONE DURAMATE SHEET 1 OF	1		