


Für diese Unterlage behalten wir uns alle Rechte vor, auch fuer den Fall der Patenterteilung oder Gebrauchsmustererteilung. Sie darf ohne unsere vorherige schriftliche Zustimmung weder vervielfältigt noch sonstwie benutzt, noch Dritten zugänglich gemacht werden.

Nur rol gestempelte oder auf Laufrarte gedruckte Dokumente unterliegen dem Änderungsdienst und sind zur Fertigung freigegeben. Only red stamped or on potcard printed documents are managed. These documents are approved for production.

All Rights reserved, including possible patents or trademarks. Documents shall not be provided to a third party or duplicated in any form without prior written permission.




CAD: Creo Parametric

Additional coding
View in direction B
3:1




C1TBATO-ED08PN-0000
Material-ID: 50298610
Mechanical coding: B
Color coding: red


Only insert
View in direction A
6:1




C1TAATO-ED08PN-0000
Material-ID: 50298609
Mechanical coding: A
Color coding: light brown



C1TCAATO-ED08PN-0000
Material-ID: 50298611
Mechanical coding: C
Color coding: blue



C1TDATO-ED08PN-0000
Material-ID: 50298612
Mechanical coding: D
Color coding: green



Delivery condition
2:1

Technical information:


- Current load: 5A (with AWG22) acc. to SAE-AS39029D
- Rated voltage: <50 V AC / <75 V DC (SELV acc. IEC 61140:2016) 1)
- Test voltage: 750 V AC (acc. EIA-364-20F:2019, sea level)
- For technical information, materials and surfaces see datasheet D00016301
- For useable accessories see datasheet D00016302
- For an assembly instruction see datasheet D00016303

1) In case that other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. In this context, lower voltage ratings may be valid.

2) For further contact information and crimping instructions see datasheet D00016300

All datasheets available at www.odu.de

Bei den hier dargestellten ODU-Steckverbindern handelt es sich nach DIN EN 61984:2009 um Steckverbinder ohne Schaltleistung (COC) !
/the pictured ODU-connectors are in relation to DIN EN 61984:2009 connectors without switching capacity (COC) !



Contact	Material-ID	Wire Size
#22D	50258807	AWG 22-26

		Benennung/description: Threaded Plug AMC Series T		Werkstoff: material: seeBOM
Allgemeintoleranz/general tol.: DIN ISO 2768-mH Tolerierung / Tolerancing: DIN ISO 8015		Zeichnungs-Nr.: Drawing-Id.: 00196432		Maßstab: scale: 3:1
Status/state: Approved		Version: revision: -		Format: size: A3
Erstellt/prepared	12.02.2021	fheitzinger	Material-Nr.: Material-Id.: C1T_ATO-ED08PN-0000	
Geaendert/revised	12.02.2021	fheitzinger		
Freigabe/released	13.04.2021	chobmaier	ODU-Nr.: ODU-Id.: C1T_ATO-ED08PN-0000	
ODU-MUEHLDORF	Datum/date	Name/name	Ursprung/origin.: sheet: 1	