



Additional coding
View in direction B





S1TBAT0-ED08PN-0000

Part-ID: 50295324
Mechanical coding: B
Color coding: red

Only insert
View in direction A
6:1




Keying indication
Color coding




S1TAAT0-ED08PN-0000

Part-ID: 50295323
Mechanical coding: A
Color coding: light brown



S1TCAAT0-ED08PN-0000

Part-ID: 50295325
Mechanical coding: C
Color coding: blue



Delivery condition
1:1

Technical information:

- Current load: 5A (with AWG22) acc. to SAE-AS39029D
- Rated voltage: <50 V AC / <75 V DC (SELV acc. IEC 61140:2016) 1)
- Test voltage: 750 V AC (acc. EIA-364-20F:2019, sea level)
- For technical information, materials and surfaces see datasheet D00016301
- For useable accessories see datasheet D00016302
- For an assembly instruction see datasheet D00016303


1) In case that other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. In this context, lower voltage ratings may be valid.

2) For further contact information and crimping instructions see datasheet D00016300

All datasheets available at www.odu.de

Bei den hier dargestellten ODU-Steckverbindern handelt es sich nach DIN EN 61984:2009 um Steckverbinder ohne Schaltleistung (COC) !
/the pictured ODU-connectors are in relation to DIN EN 61984:2009 connectors without switching capacity (COC) !

Pin 2)
6:1



Contact	Material-ID	Wire Size
#22D	50258807	AWG 22-26

 Allgemeintoleranz/general tol.: DIN ISO 2768-mH Tolerierung / Tolerancing: DIN ISO 8015		Benennung/description: Push-Pull Plug AMC Series T		Werkstoff: material: see BOM
		CAD-Nr.: design-ID: 00191403		Maßstab: scale: 3:1
Status/state: Approved	Version: revision: -	Teile-ID: part-ID:		Format: size: A3
Erstellt/prepared 09.11.2020	fheitzinger	Oxaion-Nr.:		Einheit: dim.: mm
Geaendert/revised 09.11.2020	fheitzinger	S1T_AT0-ED08PN-0000		Bl.:
Freigabe/released 12.04.2021	chobmaier			sheet: 1
ODU-MUEHLDOERF	Datum/date	Ursprung/origin.:		