


- NOTES:
- 1. FINISHED CABLE ASSEMBLY TO BE COILED
  - 2. OVERMOLD BOOT MATERIAL: UV PBT, BLACK
  - 3. ELECTRICAL TEST: 100% CONTINUITY
  - 4. ALL DIMENSIONS ARE REFERENCE ONLY EXCEPT WHEN NOTED WITH TOLERANCE

ASS'Y P/N	"X" DIM.
CA168804SP03990	3 FT. 3 1/2 IN. ± 2 IN. [1M ±50.8mm]
CA168804SP07990	6 FT. 7 IN. ± 2 IN. [2M ±50.8mm]
CA168804SP19790	16 FT. 5 IN. ± 4 IN. [5M ±101.6mm]
CA168804SP39490	32 FT. 9 3/4 IN. ± 8 IN. [10M ±203.2mm]
CA168804SPXXX90	

CABLE LENGTH IN "INCHES"



DIMENSIONS IN BRACKET [ ] ARE METRIC.

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: \_\_\_\_\_

DATE: \_\_\_\_\_

RoHS COMPLIANT

WIRE COLOR CODE, END "A"			
POS. 1	POS. 2	POS. 3	POS. 4
BLK	WHT	BLU	BRN

A	AN	06-07-21	DRAWING CREATED PER DOR 21-109360DS		
REV.	INIT.	DATE	DESCRIPTION		
	AN	06-07-21	ORIG. DRAWN BY: AN	DATE: 06-07-21	 601 E. WILDWOOD VILLA PARK, IL 60181
			CHECKED BY:		
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			APPROVED BY:		TITLE: CABLE ASSEMBLY (4) #22 SOCKET CONTACTS INSTA-CLICK™ MICRO-CON-X STANDARD PRODUCT
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			SCALE: NTS	SIZE: B	
= CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			FILE: CA168804SPXXX90	SHEET 1 OF 1	CUSTOMER: CA168804SPXXX90
			DIRECTORY: SLW		
			PART NUMBER:	REV A	