

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	19JAN2022	SCB	PS


NOTES:

1 MATERIALS & FINISH
HOUSING : PA66, UL94 V0, COLOR - LIGHT GREEN
CONTACT : COPPER ALLOY, TIN PLATED

2. ELECTRICAL
RATED VOLTAGE : 150V
RATED CURRENT : 4A
INSULATION RESISTANCE : >2000 M Ohm (500V DC)


3. OPERATING TEMPERATURE RANGE : -40°C TO +105°C

4 TOLERANCE NOT CUMULATIVE



RECOMMENDED PCB LAYOUT

41.90	16	1-2385002-6
39.40	15	1-2385002-5
36.90	14	1-2385002-4
34.40	13	1-2385002-3
31.90	12	1-2385002-2
29.40	11	1-2385002-1
26.90	10	1-2385002-0
24.40	9	2385002-9
21.90	8	2385002-8
19.40	7	2385002-7
16.90	6	2385002-6
14.40	5	2385002-5
11.90	4	2385002-4
9.40	3	2385002-3
6.90	2	2385002-2
DIM A	NO. OF POS	TE PN



2385002-3 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11JAN2022 SHRICHARANA B	TE Connectivity NAME TERMINAL BLOCK, 90 DEG HEADER, PITCH 2.5mm, TAIL LENGTH 3.8mm - SIZE CAGE CODE DRAWING NO RESTRICTED TO A3 00779 C-2385002		
DIMENSIONS: mm		CHK 11JAN2022 SUBHASREE S			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 11JAN2022 PRASHANTH S			
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		PRODUCT SPEC 108-32299 APPLICATION SPEC 114-32242 WEIGHT -			
MATERIAL		CUSTOMER DRAWING			SCALE 5:1 SHEET 1 OF 1 REV A