

1		2			3			4		
COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	
△					△					
△					△					
△					△					

ABCDEF

Notes:

- 1 THE RECOMMENDED CLAMP TORQUE OF REF. NO. 10 TO BE 0.2 TO 0.3 N·m. LOCTITE 242, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. 10 FROM LOOSENING.
- 2 ROTATION EXAMPLES OF REF. NO. 1 AND 6 ARE SHOWN.
- 3 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE. PLEASE CONFIRM BEFORE THE USE.

5	BRASS	NICKEL PLATING
4	DIALYL PHTHALATE	(BLACK) UL94V-0
3	DIALYL PHTHALATE	(BLACK) UL94V-0
2	COPPER ALLOY	SILVER PLATING 5μm min.
1	BRASS	NICKEL PLATING

10	BRASS	NICKEL PLATING
9	PHOSPHOR BRONZE	NICKEL PLATING JIS B 1251
8	BRASS	NICKEL PLATING JIS B 1101 M2×10
7	BRASS	NICKEL PLATING
6	BRASS	NICKEL PLATING

NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
5	BRASS	NICKEL PLATING	10	BRASS	NICKEL PLATING
4	DIALYL PHTHALATE	(BLACK) UL94V-0	9	PHOSPHOR BRONZE	NICKEL PLATING JIS B 1251
3	DIALYL PHTHALATE	(BLACK) UL94V-0	8	BRASS	NICKEL PLATING JIS B 1101 M2×10
2	COPPER ALLOY	SILVER PLATING 5μm min.	7	BRASS	NICKEL PLATING
1	BRASS	NICKEL PLATING	6	BRASS	NICKEL PLATING

CODE NO. (OLD)

DRAWN: I. Suguchi 21.06.07

DESIGNED: I. Suguchi 21.06.07

CHECKED: H. Kobayashi 21.06.07

APPROVED: T. Komatsu 21.06.09

RELEASED

DRAWING NO. EDC4-003127-76-00

PART NO. RM15TP-10S(76)

CODE NO. CL109-0055-8-76

TO

R

DRAWING NO. EDC4-003127-76-00

PART NO. RM15TP-10S(76)

CODE NO. CL109-0055-8-76

1

1

1234FORM NO. 22B