

1					2					3					4				
COUNT	DESCRIPTION OF REVISIONS			BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS			BY	CHKD	DATE						
△							△												
△							△												
△							△												

NOTES

- 1 ROTATION EXAMPLES OF REF.NO. ① AND ⑧ ARE SHOWN.
- 2 THE RECOMMENED TORQUE OF REF.NO. ⑧: 2 TO 3N · m.
- 3 THE RECOMMENED TORQUE OF REF.NO. ⑪: 0.3 TO 0.4N · m.

11	STEEL	NICKEL PLATING	THE WIDTH ACROSS OF A HEXAGON SOCKET: 1.27
10	BRASS	NICKEL PLATING	
9	ZINC ALLOY	MATTE FINISH NICKEL PLATING	
8	ZINC ALLOY	MATTE FINISH NICKEL PLATING	
7	BRASS	NICKEL PLATING	
6	BERYLLIUM COPPER	NICKEL PLATING	
5	BRASS	MATTE FINISH NICKEL PLATING	

NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
4	DIALYL PHTHALATE	(BLACK) UL94V-0			
3	DIALYL PHTHALATE	(BLACK) UL94V-0			
2	COPPER ALLOY	SILVER PLATING 5μm min.			
1	ZINC ALLOY	MATTE FINISH NICKEL PLATING			

CODE NO. (OLD)		DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
CL		T. Suzuki '21.06.03	T. Suzuki '21.06.03	H. Kobayashi '21.06.07	T. Komatsu '21.06.09	

DRAWING NO.		PART NO.	
EDC4-112326-76-00		RM12BPE-3S(76)	
SCALE 2 : 1		CODE NO.	
UNITS mm		CL109-0424-2-76	

HRS HIROSE ELECTRIC CO., LTD.

FORM NO. 228

TO
R

