

REVISIONS						
REV	ECO	DESCRIPTION	DATE	BY	APPR	
A1	-	RELEASE NEW DRAWING	04/JAN/22	IAN	TOMMY	





2X RECOMMENDED TORQUE: 1.5-2.0 NM-

NOTES: UNLESS OTHERWISE SPECIFIED

1. RECEPTACLE MATERIAL:

SHELL: ALUMINUM ALLOY, ANODIZE

INSERT AND RETAINING RING: THERMOPLASTIC

SEAL: SILICONE RUBBER

2. BACKSHELL MATERIAL:

SHELL: ALUMINIUM ALLOY, NICKEL PLATED; LATCH SEGMENT: ALUMINIUM ALLOY, NICKEL PLATED; SCREW AND LOCK WASHER: STAINLESS STEEL;


BUSHING: EPDM.

- 3. SPECIFICATIONS:
 - 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
 - 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
 - 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
 - 3.4 MOISTURE RESISTANCE:


IP68(IM OF WATER FOR A PERIOD OF 24 HOURS, MATED CONDITION):

IP69K(MATED CONDITION).

- 3.5 MATING CYCLE DURABILITY: 100 CYCLES
- 3.6 RoHS COMPLIANT
- 4. APPLY TO CABLE OD SIZE: Ø11.20-Ø24.08 . CAN BE USED:
- 4.1. WITH LARGE AND SMALL BUSHINGS IN PLACE.
- 4.2. WITH ONLY LARGE BUSHING IN PLACE.
- 4.3. WITH BOTH BUSHINGS REMOVED.
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
- 6. SEE SPECIFIC RECEPTACLE DRAWING FOR:
 - 6.1 CONTACT SIZE AND WIRE RANGE.
 - 6.2 RETAINING RING COLOR.
 - 6.3 MATING PART(S).
 - 6.4 CONTACT LAYOUT AND ALL OTHER SPECIFICATIONS.







- Ø18.8 LARGE BUSHING

AHDBM04-24-91PN-059			N-059	REF:HD34-24-91PN-059						
QUANTITY	ITY PART NUMBER			DESCRIPTION			П	TEM		
	MATER				ALS	S LI	ST			
UNLESS OTHERWISE SPECIFIED SIGNATURES DATE			DATE	Λτε Λ l						
1) All dimensions a 2) Tolerances are a 1 PL DEC ±0.30		DRAWN:	IAN.XIAO	O4/JAN/22 Amphei		= Amnnenni				
2 PL DEC ±0.15 3 PL DEC ±0.08	Angles ±1°	CHECKED:	SULLEN.ZHANG	04/JAN/22	JAN/22 Sine Systems - www.amphenol-sine.com				-	
3) Note reference	ENGINEER:			44724 Morley Drive						
MATERIAL SPECIFICA	TIONS:	APPROVAL:	TOMMY.XIE	05/JAN/22	Clinton Township, MI 48036			-		
		CUSTOMER	:	'	DURA	MATE	AHDBM RECEPT,	SIZE 24,	WD TH	HD,
			ING IS SUPPLIED F			KIT V	// CABLE CLAMP E	BACKSHE	LL	
PROCESS SPECIFICATIONS:		INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMFNISIONS ARE SUBJECT TO NORMAI		B	C-	AHDBM04-24-	91PN-05	9 A	sion 1	
NEXT ASS'Y:			URING VARIATION:	S.	SCALE: N	ONE	DURAMATE	SHEET 1	OF 1	1

TITLE: DURAMATE AHDBM RECEPT, SIZE 24, WD THD,KIT,RECPT AND BACKSHELL,SZ 24 DWG NO: AHDBM 04-24-91PN-059

SH:

AT Series™ - Contact Size 16 Options

Machined Contacts, Sockets & Pins						
Part Number	Description	Size	AWG	Туре		
AT60-215-1631	Male Contact - Pin, Gold-plated	16	14	Machined		
AT62-209-1631	Female Contact - Socket, Gold-plated	16	14	Machined		
AT60-215-16141	Male Contact - Pin, Nickel-plated	16	14	Machined		
AT62-209-16141	Female Contact - Socket, Nickel-plated	16	14	Machined		
AT60-202-1631	Male Contact - Pin, Gold-plated	16	16-20	Machined		
AT62-201-1631	Female Contact - Socket, Gold-plated	16	16-20	Machined		
AT60-202-16141	Male Contact - Pin, Nickel-plated	16	16-20	Machined		
AT62-201-16141	Female Contact - Socket, Nickel-plated	16	16-20	Machined		
AT60-202-1631-22	Male Contact - Pin, Gold-plated	16	22-24	Machined		
AT62-201-1631-22	Female Contact - Socket, Gold-plated	16	22-24	Machined		
AT60-202-16141-22	Male Contact - Pin, Nickel-plated	16	22-24	Machined		
AT62-201-16141-22	Female Contact - Socket, Nickel-plated	16	22-24	Machined		

Tooling - Machined Contacts					
Part	Part Number	Description			
	CA-5D12	Universal Hand Crimp Tool, Size 12/16/20 (Machined contacts only)			
3	CA-5E12	Pneumatic Crimp Tool, Size 12/16/20 (Machined contacts only)			

	Contact Removal Tools					
Part	Part Number	Description				
3	ATRT-100	Used for removal of contacts for A Series™ products				
	AT11-310-1605	Contact Removal Tool, Plastic, Size 16				
	A114017	Sealing Plug, Size 16, White				

Stamped & Formed Contacts, Sockets & Pins							
Part Number	Description	Size	AWG	Type			
AT60-14-0144	Male Contact - Pin, Gold-plated	16	14-16	Stamped & Formed			
AT62-14-0144	Female Contact - Socket, Gold-plated	16	14-16	Stamped & Formed			
AT60-14-0122	Male Contact - Pin, Nickel-plated	16	14-16	Stamped & Formed			
AT62-14-0122	Female Contact - Socket, Nickel-plated	16	14-16	Stamped & Formed			
AT60-16-0144	Male Contact - Pin, Gold-plated	16	16-18	Stamped & Formed			
AT62-16-0144	Female Contact - Socket, Gold-plated	16	16-18	Stamped & Formed			
AT60-16-0122	Male Contact - Pin, Nickel-plated	16	16-18	Stamped & Formed			
AT62-16-0122	Female Contact - Socket, Nickel-plated	16	16-18	Stamped & Formed			
AT60-16-0644	Male Contact - Pin, Gold-plated	16	18-20	Stamped & Formed			
AT62-16-0644	Female Contact - Socket, Gold-plated	16	18-20	Stamped & Formed			
AT60-16-0622	Male Contact - Pin, Nickel-plated	16	18-20	Stamped & Formed			
AT62-16-0622	Female Contact - Socket, Nickel-plated	16	18-20	Stamped & Formed			
AT60-16-0844	Male Contact - Pin, Gold-plated	16	20-22	Stamped & Formed			
AT62-16-0844	Female Contact - Socket, Gold-plated	16	20-22	Stamped & Formed			
AT60-16-0822	Male Contact - Pin, Nickel-plated	16	20-22	Stamped & Formed			
AT62-16-0822	Female Contact - Socket, Nickel-plated	16	20-22	Stamped & Formed			

Tooling - Stamped & Formed Contacts					
Part	Part Number	Description			
	MFX-3950	Crimp Die - Size 16, 18-20AWG (S&F contacts only)			
	MFX-3953	Crimp Die - Size 16, 16-18AWG (S&F contacts only)			
	MFX-3975	Crimp Die - Size 16, 14-16AWG (S&F contacts only)			
	MFX-3990	Crimp Die - Size 16, 20-22AWG (S&F contacts only)			
	ATT-16-00	Hand Crimp Tool - Size 16, 14-16AWG (S&F contacts only)			
	ATT-16-01	Hand Crimp Tool - Size 16, 18-20AWG (S&F contacts only)			
	ATT-1612-03	Hand Crimp Tool - Size 16, 20-22AWG (S&F contacts only)			

Amphenol Sine Systems 44724 Morley Drive Clinton Township, MI 48036 USA www.amphenol-sine.com 09/2021

MagnaMate™ ATHP - DuraMate™ AHDP - DuraMate™ AHDM Series - Contact Size 12 Options

Machined Contacts, Sockets & Pins						
Part Number	Size	AWG	Type			
AT60-204-12141-10	Male Contact - Pin, Nickel-plated	12	10-12	Machined		
AT62-203-12141-10	Female Contact - Socket, Nickel-plated	12	10-12	Machined		
AT60-220-1231	Male Contact - Pin, Gold-plated	12	12-14	Machined		
AT62-210-1231	Female Contact - Socket, Gold-plated	12	12-14	Machined		
AT60-204-12141	Male Contact - Pin, Nickel-plated	12	12-14	Machined		
AT62-203-12141	Female Contact - Socket, Nickel-plated	12	12-14	Machined		

DiagnosticGrade™ Machined Contacts, Sockets & Pins • Smaller AWG for Diagnostic Applications • Gold-plated • Increased Mating Cycles • Cost-effective						
Part Number	Part Number Description Size AWG Type					
65-54749	Male Contact - DiagnosticGrade™, Pin, Gold-plated	12	20	Machined		
AT62-210-1231-1820	Female Contact - DiagnosticGrade™, Socket, Gold-plated	12	20	Machined		

Tooling - Machined Contacts					
Part	Part Number	Description			
	CA-5D12	Universal Hand Crimp Tool, Size 12/16/20 (Machined contacts only)			
33	CA-5E12	Pneumatic Crimp Tool, Size 12/16/20 (Machined contacts only)			

Contact Removal Tools					
Part	Part Number	Description			
	AT11-337-1205	Contact Removal Tool, Plastic, Size 12			
	A114017	Sealing Plug, Size 12, White			

Stamped & Formed Contacts, Sockets & Pins						
Part Number	nber Description			Туре		
AT60-12-0244	Male Contact - Pin, Gold-plated	12	10-12	Stamped & Formed		
AT62-12-0244	Female Contact - Socket, Gold-plated	12	10-12	Stamped & Formed		
AT60-12-0222	Male Contact - Pin, Nickel-plated	12	10-12	Stamped & Formed		
AT62-12-0222	Female Contact - Socket, Nickel-plated	12	10-12	Stamped & Formed		
AT60-12-0144	Male Contact - Pin, Gold-plated	12	12-14	Stamped & Formed		
AT62-12-0144	Female Contact - Socket, Gold-plated	12	12-14	Stamped & Formed		
AT60-12-0166	Male Contact - Pin, Nickel-plated	12	12-14	Stamped & Formed		
AT62-12-0166	Female Contact - Socket, Nickel-plated	12	12-14	Stamped & Formed		

Tooling - Stamped & Formed Contacts					
Part	Part Number	Description			
	MFX-3973	Crimp Die - Size 12 (S&F contacts only)			
	MFX-3985	Crimp Die - Size 12 (S&F contacts only) 10-12AWG -02XX Series			
	ATT-12-00	Hand Crimp Tool - Size 12, 12AWG (S&F contacts only)			
	ATT-12-01	Hand Crimp Tool - Size 12, 10AWG (S&F contacts only)			

Amphenol Sine Systems 44724 Morley Drive Clinton Township, MI 48036 USA www.amphenol-sine.com 01/2022

ATHD Series™ - Contact Size 8 Options

Machined Contacts, Pins and Sockets					
Part Number	Description		AWG	Туре	Amps
AT60-204-08141	Male Contact - Pin, Copper Alloy, Nickel-Plated	8	8-10	Machined	60A
AT62-203-08141	Female Contact - Socket, Copper Alloy, Nickel-Plated	8	8-10	Machined	60A
AT60-204-08141-16	Male Contact - Pin, Copper Alloy, Nickel-Plated		6	Machined	60A
AT62-203-08141-16	Female Contact - Socket, Copper Alloy, Nickel-Plated	8	6	Machined	60A

Tooling - Machined Contacts					
Part	Part Number	Description			
	WA23	Heavy Duty Pneumatic Crimp Tool -Uses Universal Positioner Part No. WA23-101DA and Crimp Locator MFX-3961			
	WA23-2	Die Assembly -for CA-5E12 Heavy Duty Pneumatic Crimp Tool, Size 8			
•	WA23-3	Die Assembly -for CA-5E12 Heavy Duty Pneumatic Crimp Tool, Size 6			
Waging St.	WA23-10	Contact Locator, Size 6 and Size 8			
THE AND	96-978-22	Crimper and Dies -for Size 10mm ² -185mm ² Wires			

Contact Removal Tools				
Part	Part Number	Description		
	AT114008	Contact Removal Tool, Plastic, Size 8, 8-10AWG		