


Nov.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



Notes 1 One example of the rotation of REF.NO. ⑥ to REF.NO. ① is shown.
 2 The recommended clamp torque of REF.NO. ⑥ : 2 to 3N·m.

3 Across flats of hexagon socket of REF.NO. ⑤ : 1.27.
 The recommended clamp torque of 0.3 to 0.4N·m.
 4 LOCTITE 243, HENKEL JAPAN or equivalent is recommended to prevent REF.NO. ⑥ and ① from loosening.
 5 The cable pull and twisting strength and Other characteristics may differ, depending on the cable structure. Please confirm before the use.

6	Zinc alloy	Matte finish nickel plating			
5	Brass	Nickel plating	11	Steel	Nickel plating M2.6 X 0.45 X 2
4	Diallylphthalate	(Black) UL94V-0	10	Brass	Nickel plating M2 X 0.4 X 10
3	Diallylphthalate	(Black) UL94V-0	9	Phosphor bronze	Nickel plating
2	Copper alloy	Silver plating 2μm min.	8	Stainless steel	
1	Zinc alloy	Matte finish nickel plating	7	Zinc alloy	Matte finish nickel plating
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
HRS HIROSE ELECTRIC CO., LTD.		APPROVED : TP. KOMATSU 20210524	DRAWING NO. EDC-028092-76-00				
		CHECKED : HY. KOBAYASHI 20210521	PART NO. RM15QPS-10PH(76)				
		DESIGNED : TY. SUZUKI 20210521	CODE NO. CL0109-0851-3-76				
		DRAWN : KR. SUZUKI 20210519		1			