







RECOMMENDED
PCB LAYOUT

▲ CIRCUIT: SPST

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. CONTACT RATING: 32VDC, 50mA
4. CONTACT RESISTANCE: 100 m Ω MAX.
5. INSULATION RESISTANCE: 1G Ω MIN @ 500VDC.
- ▲ 6. OPERATING FORCE: 300 $\pm$ 75gf
7. TRAVEL: 0.25 +0.1/-0.15mm
8. OPERATING TEMPERATURE: -40°C to +85°C
9. STORAGE TEMPERATURE: -55°C to +85°C
10. OPERATING LIFE: 150,000 CYCLES
11. ▲ DENOTES CRITICAL PARAMETERS
12. CONTACT MATERIAL: SILVER
13. INGRESS PROTECTION IP67
14. PARTS TO BE PACKAGED IN TAPE & REEL, 3000 PIECES PER REEL

▲ ACTUATOR
COLOR: WHITE

REV	ECO NO	DESCRIPTION	DATE	BY	 E-SWITCH®				OBJECT ID
A	ECO-101055	RELEASE	06/16/22	JS	TITLE TL6330BF300Q				100122050
					SCALE	DATE	DR	DWG	REV
					8:1	5/24/2022	JS	P006334	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED