



REVISIONS								
REV	ECO	DESCRIPTION	DATE	BY	APPR			
A1		RELEASE NEW DRAWING	12MAY20	VITO	TOMMY			
A2		MODIFY PRODUCT NAME	11AUG20	IAN	TOMMY			





						_
	AHDP04-2	4-23SN-SRA		REF:HDP24-24-23SN	Т	9
	PART NUMBER			DESCRIPTION	ITEM	1-
QUANTITY		MA	TERI	ALS LIST		┢
All dimensions a Tolerances are a	UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows:		11AUG20	Amphenol		
1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08		CHECKED: ORION	12AUG20	Sine Systems - www.amphenol-sine.com		

ı		APPROVAL:	TOMMY	13AUG20			Clinton Township, MI 48	030		
ı	MATERIAL SPECIFICATIONS:		I UMM I	IJAUGZU						
ı		CUSTOMER:			1		RECEPT., SIZE 24, 23-5	CKE	Τ,	
ı			G IS SUPPLIED FO		1	NORMAL	. SEAL, SRA, DURAMA	ΓΕ AHD	P SERIE	S
	PROCESS SPECIFICATIONS:	SPECIFICATIO SHOWN HERE THE AMPHENO OF REPRODUC	I ONLY. DESIGN F INS AND PERFOR ON ARE THE PRO DL CORPORATION CTION ARE IMPLII ARE SUBJECT TO	MANCE DATA OPERTY OF N. NO RIGHTS ED. ALL	B	C-	AHDP04-24-2	3SN-	SRA	A PEN
ı	NEXT ASSY:		ING VARIATIONS		SCALE: N	IONE	DURAMATE	SHEET	1 OF	-

44724 Morley Drive

SCALE: NONE DURAMATE SHEET 1 OF 1 DWG NO: AHDP04-24-23SN-SRA REV: A2 SH:


NOTES: UNLESS OTHERWISE SPECIFIED

MATERIAL:

HOUSING: THERMOPLASTIC; BLACK SEAL: SILICONE RUBBER


2. MODIFICATIONS: SMOOTH RING ADAPTER; STANDARD DIA. WIRE SEAL

- 3. SPECIFICATIONS:
 - 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
 - 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
 - 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
 - 3.4 MOISTURE RESISTANCE: IP67&IP69K (MATED CONDITION).
 - 3.5 MATING CYCLE DURABILITY: 100 CYCLES
 - 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP06-24-23P* (* = SEAL TYPE)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL WIRE	CURRENT
SIZE	O.D.	O.D.	RANGE	RATING
16	2.54 mm (.100in)	3.40 mm (.134 in)	14-20 AWG (2.0-0.5mm ²)	

7. RECEPTACLE IS SUPPLIED WITH DUST CAP.



MOUNTING HOLE

RECOMMENDED PANEL THICKNESS:1.6 TO 4.7MM

AT Series™ - Contact Size 16 Options

Machined Contacts, Sockets & Pins							
Part Number	Description		AWG	Туре			
AT60-215-1631	Male Contact - Pin, Gold-plated		14	Machined			
AT62-209-1631	Female Contact - Socket, Gold-plated	16	14	Machined			
AT60-215-16141	Male Contact - Pin, Nickel-plated	16	14	Machined			
AT62-209-16141	Female Contact - Socket, Nickel-plated	16	14	Machined			
AT60-202-1631	Male Contact - Pin, Gold-plated	16	16-20	Machined			
AT62-201-1631	AT62-201-1631 Female Contact - Socket, Gold-plated		16-20	Machined			
AT60-202-16141	0-202-16141 Male Contact - Pin, Nickel-plated		16-20	Machined			
AT62-201-16141	Female Contact - Socket, Nickel-plated	16	16-20	Machined			
AT60-202-1631-22	Male Contact - Pin, Gold-plated	16	22-24	Machined			
AT62-201-1631-22 Female Contact - Socket, Gold-plate		16	22-24	Machined			
AT60-202-16141-22 Male Contact - Pin, Nickel-plated		16	22-24	Machined			
AT62-201-16141-22 Female Contact - Socket, Nickel-plated		16	22-24	Machined			

Tooling - Machined Contacts					
Part	Part Number	Description			
	CA-5D12	Universal Hand Crimp Tool, Size 12/16/20 (Machined contacts only)			
CA-5E12		Pneumatic Crimp Tool, Size 12/16/20 (Machined contacts only)			

	Contact Removal Tools					
Part	Part Number	Description				
	ATRT-100	Used for removal of contacts for A Series™ products				
	AT11-310-1605	Contact Removal Tool, Plastic, Size 16				
	A114017	Sealing Plug, Size 16, White				

Stamped & Formed Contacts, Sockets & Pins							
Part Number Description		Size	AWG	Type			
AT60-14-0144	60-14-0144 Male Contact - Pin, Gold-plated			Stamped & Formed			
AT62-14-0144	Female Contact - Socket, Gold-plated	16	14-16	Stamped & Formed			
AT60-14-0122	Male Contact - Pin, Nickel-plated	16	14-16	Stamped & Formed			
AT62-14-0122	Female Contact - Socket, Nickel-plated	16	14-16	Stamped & Formed			
AT60-16-0144	Male Contact - Pin, Gold-plated	16	16-18	Stamped & Formed			
AT62-16-0144	Female Contact - Socket, Gold-plated	16	16-18	Stamped & Formed			
AT60-16-0122	Male Contact - Pin, Nickel-plated	16	16-18	Stamped & Formed			
AT62-16-0122	Female Contact - Socket, Nickel-plated	16	16-18	Stamped & Formed			
AT60-16-0644	Male Contact - Pin, Gold-plated	16	18-20	Stamped & Formed			
AT62-16-0644	Female Contact - Socket, Gold-plated	16	18-20	Stamped & Formed			
AT60-16-0622	Male Contact - Pin, Nickel-plated	16	18-20	Stamped & Formed			
AT62-16-0622	Female Contact - Socket, Nickel-plated	16	18-20	Stamped & Formed			
AT60-16-0844	Male Contact - Pin, Gold-plated	16	20-22	Stamped & Formed			
AT62-16-0844	Female Contact - Socket, Gold-plated	16	20-22	Stamped & Formed			
AT60-16-0822	Male Contact - Pin, Nickel-plated	16	20-22	Stamped & Formed			
AT62-16-0822	Female Contact - Socket, Nickel-plated	16	20-22	Stamped & Formed			

Tooling - Stamped & Formed Contacts					
Part	Part Number	Description			
	MFX-3950	Crimp Die - Size 16, 18-20AWG (S&F contacts only)			
	MFX-3953	Crimp Die - Size 16, 16-18AWG (S&F contacts only)			
	MFX-3975	Crimp Die - Size 16, 14-16AWG (S&F contacts only)			
	MFX-3990	Crimp Die - Size 16, 20-22AWG (S&F contacts only)			
	ATT-16-00	Hand Crimp Tool - Size 16, 14-16AWG (S&F contacts only)			
	ATT-16-01	Hand Crimp Tool - Size 16, 18-20AWG (S&F contacts only)			
	ATT-1612-03	Hand Crimp Tool - Size 16, 20-22AWG (S&F contacts only)			

Amphenol Sine Systems 44724 Morley Drive Clinton Township, MI 48036 USA www.amphenol-sine.com 09/2021