


	REVISIONS						
REV	ECO	DESCRIPTION	DATE	BY	APPR		
A1	-	RELEASE NEW DRAWING	18MAY20	IAN	TOMMY		
A2	-	MODIFY PRODUCT NAME	11AUG20	IAN	TOMMY		







REE-HDP26-24-19SE

NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:


HOUSING: THERMOPLASTIC; BLACK SEAL: SILICONE RUBBER

- 2. MODIFICATIONS: SMOOTH RING ADAPTER (SRA); REDUCED DIA. WIRE SEAL;
- 3. SPECIFICATIONS:
 - 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
 - 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
 3.4 MOISTURE RESISTANCE: IP67&IP69K (MATED CONDITION).
 3.5 MATING CYCLE DURABILITY: 100 CYCLES

 - 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP04-24-19P* (* = SEAL TYPE)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

6 CONTACT SIZE AND WIRE RANGE:

(CONTACT SIZE	MIN. INSUL O.D.	MAX. INSUL O.D.	TYPICAL WIRE RANGE	CURRENT RATING
	12	2.46 mm (.097 in)	4.01 mm (.158 in)	10-14 AWG (6.0-2.0mm²)	25 AMPS
	16	1.35 mm (.053 in)	3.05 mm (.120 in)	14-20 AWG (2.0-0.5mm²)	13 AMPS



SMOOTH RING ADAPTER - BLUE

AHDP06-24-19SR-SRA

	AUDL00-2	4-1901-	SKA	KEI	F:HDP20-24-195E		
	PART N	IUMBEF	₹		DE	SCRIPTION	
QUANTITY			MAT	ERI	ALS LI	ST	
	WISE SPECIFIED	SIGI	ATURES	DATE		mnha	
1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 Fractions ±1/64		DRAWN:	OAIX.NAI	11AUG20	Amphe		
2 PL DEC ±0.15 3 PL DEC ±0.08	Angles ±1°	CHECKED:	ORION.LI	12AUG20	Sin	e Systems - www.amphe	enol-si
3) Note reference = X		ENGINEER:				44724 Morley Drive	2020
MATERIAI SPECIFICA	TIONS:	APPROVAL:	TOMMYXIE	13AUG20		Clinton Township, MI 48	0000
		CUSTOMER:				PLUG, SIZE 24, 19-S	OCK
PROCESS SPECIFICA	TIONS		IG IS SUPPLIED I		RD01 SE	AL,SRA,DURAMAT	E AH
PROCESS SPECIFICA	HUNS:	SHOWN HERI	ONS AND PERFO EON ARE THE PE	ROPERTY OF	SIZE TYPE	DWG NO:	۸۸۶
		OF REPRODU	IOL CORPORATI ICTION ARE IMP ARE SUBJECT T	LIED. ALL	B C-	AHDP06-24-1	95 t
NEXT ASS'Y:			RING VARIATION	IS.	SCALE: NONE	DURAMATE	SHEET

nenol amphenol-sine.com

ITEM ·

19-SOCKET, MATE AHDP SERIES

AT Series™ - Contact Size 16 Options

	Machined Contacts, Sockets & Pins					
Part Number	Description	Size	AWG	Туре		
AT60-215-1631	Male Contact - Pin, Gold-plated	16	14	Machined		
AT62-209-1631	Female Contact - Socket, Gold-plated	16	14	Machined		
AT60-215-16141	Male Contact - Pin, Nickel-plated	16	14	Machined		
AT62-209-16141	Female Contact - Socket, Nickel-plated	16	14	Machined		
AT60-202-1631	Male Contact - Pin, Gold-plated	16	16-20	Machined		
AT62-201-1631	Female Contact - Socket, Gold-plated	16	16-20	Machined		
AT60-202-16141	Male Contact - Pin, Nickel-plated	16	16-20	Machined		
AT62-201-16141	Female Contact - Socket, Nickel-plated	16	16-20	Machined		
AT60-202-1631-22	Male Contact - Pin, Gold-plated	16	22-24	Machined		
AT62-201-1631-22	Female Contact - Socket, Gold-plated	16	22-24	Machined		
AT60-202-16141-22	Male Contact - Pin, Nickel-plated	16	22-24	Machined		
AT62-201-16141-22	Female Contact - Socket, Nickel-plated	16	22-24	Machined		

	Tooling - Machined Contacts				
Part	Part Number	Description			
	CA-5D12	Universal Hand Crimp Tool, Size 12/16/20 (Machined contacts only)			
3	CA-5E12	Pneumatic Crimp Tool, Size 12/16/20 (Machined contacts only)			

	Contact Removal Tools				
Part	Part Number	Description			
3	ATRT-100	Used for removal of contacts for A Series™ products			
	AT11-310-1605	Contact Removal Tool, Plastic, Size 16			
	A114017	Sealing Plug, Size 16, White			

	Stamped & Formed Contacts, Sockets & Pins					
Part Number	Description	Size	AWG	Type		
AT60-14-0144	Male Contact - Pin, Gold-plated	16	14-16	Stamped & Formed		
AT62-14-0144	Female Contact - Socket, Gold-plated	16	14-16	Stamped & Formed		
AT60-14-0122	Male Contact - Pin, Nickel-plated	16	14-16	Stamped & Formed		
AT62-14-0122	Female Contact - Socket, Nickel-plated	16	14-16	Stamped & Formed		
AT60-16-0144	Male Contact - Pin, Gold-plated	16	16-18	Stamped & Formed		
AT62-16-0144	Female Contact - Socket, Gold-plated	16	16-18	Stamped & Formed		
AT60-16-0122	Male Contact - Pin, Nickel-plated	16	16-18	Stamped & Formed		
AT62-16-0122	Female Contact - Socket, Nickel-plated	16	16-18	Stamped & Formed		
AT60-16-0644	Male Contact - Pin, Gold-plated	16	18-20	Stamped & Formed		
AT62-16-0644	Female Contact - Socket, Gold-plated	16	18-20	Stamped & Formed		
AT60-16-0622	Male Contact - Pin, Nickel-plated	16	18-20	Stamped & Formed		
AT62-16-0622	Female Contact - Socket, Nickel-plated	16	18-20	Stamped & Formed		
AT60-16-0844	Male Contact - Pin, Gold-plated	16	20-22	Stamped & Formed		
AT62-16-0844	Female Contact - Socket, Gold-plated	16	20-22	Stamped & Formed		
AT60-16-0822	Male Contact - Pin, Nickel-plated	16	20-22	Stamped & Formed		
AT62-16-0822	Female Contact - Socket, Nickel-plated	16	20-22	Stamped & Formed		

	Tooling - Stamped & Formed Contacts					
Part	Part Number Description					
	MFX-3950	Crimp Die - Size 16, 18-20AWG (S&F contacts only)				
	MFX-3953	Crimp Die - Size 16, 16-18AWG (S&F contacts only)				
	MFX-3975	Crimp Die - Size 16, 14-16AWG (S&F contacts only)				
	MFX-3990	Crimp Die - Size 16, 20-22AWG (S&F contacts only)				
	ATT-16-00	Hand Crimp Tool - Size 16, 14-16AWG (S&F contacts only)				
	ATT-16-01	Hand Crimp Tool - Size 16, 18-20AWG (S&F contacts only)				
	ATT-1612-03	Hand Crimp Tool - Size 16, 20-22AWG (S&F contacts only)				

Amphenol Sine Systems 44724 Morley Drive Clinton Township, MI 48036 USA www.amphenol-sine.com 09/2021

ATP Series™ - Contact Size 12 Options

Machined Contacts, Sockets & Pins					
Part Number	Description	Size	AWG	Туре	
AT60-204-12141-10	Male Contact - Pin, Nickel-plated	12	10-12	Machined	
AT62-203-12141-10	Female Contact - Socket, Nickel-plated	12	10-12	Machined	
AT60-220-1231	Male Contact - Pin, Gold-plated	12	12-14	Machined	
AT62-210-1231	Female Contact - Socket, Gold-plated	12	12-14	Machined	
AT60-204-12141	Male Contact - Pin, Nickel-plated	12	12-14	Machined	
AT62-203-12141	Female Contact - Socket, Nickel-plated	12	12-14	Machined	

Smaller AWG for	DiagnosticGrade™ Machined Contacts, Sockets & Pins • Smaller AWG for Diagnostic Applications • Gold-plated • Increased Mating Cycles • Cost-effective					
Part Number	Description	Size	AWG	Туре		
65-54749	Male Contact - DiagnosticGrade™, Pin, Gold-plated	12	20	Machined		
AT62-210-1231-1820	Female Contact - DiagnosticGrade™, Socket, Gold-plated	12	20	Machined		

Tooling - Machined Contacts				
Part	Part Number	Description		
	CA-5D12	Universal Hand Crimp Tool, Size 12/16/20 (Machined contacts only)		
35	CA-5E12	Pneumatic Crimp Tool, Size 12/16/20 (Machined contacts only)		

Contact Removal Tools				
Part	Part Number	Description		
refer turbs	ATRT-100	Used for removal of contacts for A Series™ products		
	AT11-337-1205	Contact Removal Tool, Plastic, Size 12		
	A114017	Sealing Plug, Size 12, White		

Stamped & Formed Contacts, Sockets & Pins					
Part Number	Description		AWG	Туре	
AT60-12-0244	Male Contact - Pin, Gold-plated	12	10-12	Stamped & Formed	
AT62-12-0244	Female Contact - Socket, Gold-plated	12	10-12	Stamped & Formed	
AT60-12-0222	Male Contact - Pin, Nickel-plated	12	10-12	Stamped & Formed	
AT62-12-0222	Female Contact - Socket, Nickel-plated	12	10-12	Stamped & Formed	
AT60-12-0144	Male Contact - Pin, Gold-plated	12	12-14	Stamped & Formed	
AT62-12-0144	Female Contact - Socket, Gold-plated	12	12-14	Stamped & Formed	
AT60-12-0166	Male Contact - Pin, Nickel-plated	12	12-14	Stamped & Formed	
AT62-12-0166	Female Contact - Socket, Nickel-plated	12	12-14	Stamped & Formed	

Tooling - Stamped & Formed Contacts				
Part	Part Number	Description		
	MFX-3973	Crimp Die - Size 12 (S&F contacts only)		
	MFX-3985	Crimp Die - Size 12 (S&F contacts only) 10-12AWG -02XX Series		
	ATT-12-00	Hand Crimp Tool - Size 12, 12AWG (S&F contacts only)		

Amphenol Sine Systems 44724 Morley Drive Clinton Township, MI 48036 USA www.amphenol-sine.com 09/2021