
** Not all features are shown in this drawing. For more detailed information, please contact your Fair-Rite representative.

UNCONTROLLED ~CATALOG~ DRAWING

| SIZE | PART NO. | REV. | REV. |



DIMENSIONS BOLD NUMBERS ARE IN MILLIMETERS

LIGHT NUMBERS ARE IN INCHES

NOTES:

- 1 CHIPS CRACKS, AND APPEARANCE TO MEET FAIR-RITE VISUAL INSPECTION CRITERIA FOR GENERIC MULTI-HOLE WOUND BEADS.
- 2 IMPEDANCE MEASURED USING A HP4191A ON A 16092A TEST FIXTURE, WITH FIXTURE COMPENSATION, AND A WIRE LENGTH CUT TO <6.35mm [<.250"].
- 3 WIRE MEETS SOLDERABILITY SPECIFICATION WHEN TESTED PER FAIR-RITE PRODUCTS CORP. SOP# ELC-57.
- 4 PART MEETS FAIR-RITE PRODUCTS CORP. SOP# ELC-55, FOR THERMAL SHOCK RESISTANCE.
- 5 RESISTIVITY > 1 X 10E6 Ohms-cm, Rdc @ 10Vdc, ACROSS "C" DIMENSION > 4 X 10E6 Ohms
- 6 WIRE LOOPS SHOULD BE UNIFORM IN LENGTH.
- 7 PART IS TO BE BULK PACKED

ELECTRICAL SPECIFICATIONS

IMPEDANCE (Ohms)								
50 MHz	100 MHz	200 MHz						
448 Min.	624 Min.	768 Min.						

JEF/	AIR-F	RITE	. F	PROD	U	CTS	COF	RP.
TITLE WOUND BEAD								
DRAWN BY	DATE	SIZE	PAF	RT NO.				REV.
D. FOOTE	11/13/2019	_	_		_			
CHKD BY		□B 2961666671						2
APPRVD BY		SCA	LE:	NONE		SHEE	T 1 0	F 1

FR# 61