



Protective Cover
Bayonet Locking Style
Plastic Version






Recommended Panel Cutout



Fiber Optic Duplex LC
Adaptor Assembly
(Supplied with dust caps)

Panel Flange
Receptacle Housing
Bayonet Locking Type
Plastic Version

Bayonet Channel x 3



Notes:

1. Material and Finish:

- Receptacle Housing, Protective Cover: Polyester (Black); UL94 V-0
- Panel Nut: Brass, Finish: Nickel Plated
- Panel Gasket: Silicon, Color: White
- Cover Gasket: Silicon, Color: White
- Tether: Polycarbonate, Color: Black

Duplex LC Adaptor Assembly:

- Housing: Mod. PPO, UL94 V-0, Color: **SM Blue/MM Beige/APC SM Green**
- Alignment Sleeves: SM Ceramic/MM Phosphor Bronze
- Dust Cap: PP, Color: Neutral transparent
- Operating Temperature: -40~C to +85~C

2. Connector can be front or rear mounted to a maximum panel thickness of 3.2mm.

3. IP67/IP68 rated when covered or fully mated with the appropriate mating connector

Description	Part Number
Plastic Duplex LC Single Mode Receptacle Assembly + Cover Assembly	17-300230
Plastic Duplex LC Multi Mode Receptacle Assembly + Cover Assembly	17-300240
Plastic Duplex LC APC Single Mode Receptacle Assembly + Cover Assembly	17-300250

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY MANNER OR FOR ANY PURPOSE WITHOUT THE WRITTEN PERMISSION OF CONEC CORPORATION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION.	Customer:			Tolerance Unless otherwise specified			Scale: 1.5:1	Dim. in mm
	Name	Title	Approval Date	0 1 2 3 ANGLES	PLC PLC PLC PLC		Autodesk Inventor	Material: See Notes
	1 x d	A21-0426	29.10.2021	Bub	2011	Date	Name	Title: IP67 Industrial Duplex LC Receptacle Assembly + Cover Assembly Plastic version
	c	1 x c	Dec/03/2015	Vincent Ke	Draw.	Mar. 04	Vincent Ke	Drawing No.: 17K1A217
b	2 x b	Sep/25/2013	Vincent Ke	Appd.	Mar. 04	J. Chaudry	Part No.: SEE ABOVE TABLE	
a	original			Norm			DIN A3	
Rev	Changes	Date	Name				Sheet 1/1	