







Mar.1.2022 Copyright 2022 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

ELV, RoHS COMPLIANT



RECOMMENDED PCB PATTERN


- NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW (REFER TO RIGHT FIG.)
USED REFLOW SYSTEM : IR IN THE AIR OR NITROGEN
NO. OF CYCLES : 2 MAX
PEAK : 250°C
OVER 230°C : 20~40s
PREHEAT : 150~180°C 60~120s
2. TEMPERATURE FOR SOLDERING IRON : 280~300°C WITHIN 2s
3. CO-PLANARITY SHALL BE 0.1mm MAX.
4. RECOMMENDED PCB THICKNESS IS 1.6mm.
5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.




3	BRASS	TIN PLATED T=0.64	6	PET	
2	BRASS	TIN PLATED T=0.64	5	PS	
1	PPS	BLACK	4	BRASS	TIN PLATED T=0.4
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED
	APPROVED : NH. NAKATA	16. 01. 13	DRAWING NO.	EDC-169254-00-00	CHECKED
	CHECKED : HS. OZAWA	16. 01. 13	PART NO.	GT25H2-8DP-2. 2H	DATE
	DESIGNED : TK. SHISHIKURA	16. 01. 13	CODE NO.	CL775-0047-4-00	
	DRAWN : TK. SHISHIKURA	16. 01. 13			

Mar.1.2022 Copyright 2022 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


PACKAGING SPECIFICATION



REEL DIMENSION(FREE)



CARDBOARD DIMENSION(FREE)



BOX SIZE

W=(405) (mm)

D=(405) (mm)

H=(39) (mm)

HRS

DRAWING NO.	EDC-169254-00-00
PART NO.	GT25H2-8DP-2.2H
CODE NO.	CL775-0047-4-00

2/2