







RECOMMENDED PCB PATTERN

USED REFLOW SYSTEM

: IR IN THE AIR OR NITROGEN

NO. OF CYCLES : 2 MAX

PEAK : 250°C

OVER 230°C : 20~40s

PREHEAT : 150~180℃

60~120s


2. TEMPERATURE FOR SOLDERING IRON

:280~300°C WITHIN 2s

3. CO-PLANARITY SHALL BE 0.1mm MAX.

4. RECOMMENDED PCB THICKNESS IS 1.6mm.


5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.




3	BRASS	TIN PLATED T=0.64	6	PET												
2	BRASS	TIN PLATED T=0.64	5	PS												
1	PPS	BLACK	4	BRASS	TIN PLATED T=0.4											
NO.	MATERIAL	FINISH , REMARKS		NO.	MATERIAL	FINISH , REMARKS										
UNITS mm				SCALE 2 : 1				COUNT	DESCRIPTION OF REVISIONS		DESIGNED		CHECKED		DATE	
 HIROSE ELECTRIC CO., LTD.		APPROVED : NH. NAKATA		16.02.29		DRAWING NO.		EDC-361744-00-00								
		CHECKED : HS. OZAWA		16.02.29		PART NO.		GT25H2-12DP-2.2H								
		DESIGNED : TK. SHISHIKURA		16.02.26		CODE NO.		CL775-0092-9-00								
		DRAWN : TK. SHISHIKURA		16.02.26				 								

Mar.1.2022 Copyright 2022 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


PACKAGING SPECIFICATION



REEL DIMENSION(FREE)



CARDBOARD DIMENSION(FREE)



BOX SIZE
W = (405) (mm)
D = (405) (mm)
H = (49) (mm)

HRS

DRAWING NO.	EDC-361744-00-00
PART NO.	GT25H2-12DP-2.2H
CODE NO.	CL775-0092-9-00

2/2