

## CONNECTORS USED:

PART DESCRIPTION	PART NAME	MANUFACTURER	QTY
PIN HEADER (INPUT SIDE CN1)	B3(7.5)B-XH-A	J.S.T	1
PIN HEADER (OUTPUT SIDE CN2)	B4B-XH-A	J.S.T	1

## MATCHING HOUSINGS & PINS:

\* NOT INCLUDED WITH THE PRODUCT.

NOT INCLUDED WITH TH	E INODUCI.		
PART DESCRIPTION	PART NAME	MANUFACTURER	QTY
SOCKET HOUSING (CN1)	XHP-7	J.S.T	1
SOCKET HOUSING (CN2)	XHP-4	J.S.T	1
TERMINAL PINS (CN1,2)	BXH-001T-P0.6 OR	J.S.T	7
	SXH-001T-P0.6		

HAND CRIMPING TOOL: YC-110R CN1,2 MANUFACTURER: J.S.T : YRS-11 CN1,2 MANUFACTURER: J.S.T

## NOTES:

A: THE 4XØ3.5 HOLES ARE CUSTOMER CHASSIS MOUNTING HOLES. ALL MUST BE SCREWED IN ORDER TO CONFORM THE VIBRATION SPEC.

B: MODEL NAME, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT AND SAFETY MARKING(FOR ONLY APPROVED PRODUCTS) ARE SHOWN ON THE NAME PLATE IN ACCORDANCE WITH THE SPECIFICATIONS.

C : COUNTRY OF MANUFACTURE WILL BE SHOWN ON THE NAME PLATE.

D: TO KEEP THE DISTANCE MORE THAN 2mm BETWEEN PC-BOARD EDGE AND CUSTOMER CHASSIS.

