





NOTES:

1. RESISTANCE @ 25°C : 10KΩ ± 1%
2. BETA VALUE (0/50°C) : 4035K ± 1%
3. OPERATING TEMPERATURE RANGE : -40°C TO +250°C.
4. THERMAL TIME CONSTANT : 15SEC IN WATER
5. VOLTAGE BREAKDOWN STRENGTH : 1500V AC FOR 3SEC.
6. INSULATION RESISTANCE : A MINIMUM OF 100MΩ @ 500VOLTS DC.
7. DISSIPATION FACTOR : 1mW/°C.
8. LASER MARKING "MOLEX-DATE CODE(MM/YY)"

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
	DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex				
▽_A = 0	mm	NTS										
▽_F = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				GLASS NTC PROBE A - 10K±1%,B4035,L300							
▽_P = 0	ANGULAR TOL ± °											
DIVISIONAL SYMBOLS	4 PLACES	±	EC NO: 718518		2022/08/04							
	3 PLACES	±	DRWN: NANDAK									
	2 PLACES	±	CHK'D: RBBHASKAR									
	1 PLACE	±	APPR: RBBHASKAR		2022/08/24							
	0 PLACES	±	INITIAL REVISION:		2022/08/24							
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION							DOCUMENT NUMBER		
				DRAWING		SERIES		2185373609		PSD	000	A1
		A3-SIZE		218537		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER		
						2185373609		GENERAL MARKET		1 OF 2		

