




NOTES:

- 1. RESISTANCE @ 25°C : 10KΩ ± 1%
- 2. BETA VALUE (0/50°C) : 3964K ± 1%
- 3. OPERATING TEMPERATURE RANGE : -40°C TO +250°C.
- 4. THERMAL TIME CONSTANT : 15SEC IN WATER
- 5. VOLTAGE BREAKDOWN STRENGTH : 1500V AC FOR 3SEC.
- 6. INSULATION RESISTANCE : A MINIMUM OF 100MΩ @ 500VOLTS DC.
- 7. DISSIPATION FACTOR : 1mW/°C.
- 8. LASER MARKING "MOLEX-DATE CODE(MM/YY)"

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
	DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex				
	mm		NTS									
	GENERAL TOLERANCES (UNLESS SPECIFIED)							GLASS NTC PROBE A -10K±1%,B3964,L300				
ANGULAR TOL ± °												
DIVISIONAL SYMBOLS	4 PLACES		±	EC NO: 718518			PRODUCT CUSTOMER DRAWING					
	3 PLACES		±	DRWN: NANDAK 2022/08/04								
	2 PLACES		±	CHK'D: RBBHASKAR 2022/08/24								
	1 PLACE		±	APPR: RBBHASKAR 2022/08/24								
	0 PLACES		±	INITIAL REVISION:								
				DRWN: RAVIKM 2022/01/28								
				APPR: RBBHASKAR 2022/02/18			DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION	
							2185363609		PSD	000	A1	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
						A3-SIZE	218536	2185363609		GENERAL MARKET		1 OF 2

