





NOTES:

1. RESISTANCE @ 25°C : 10KΩ ± 1%
2. BETA VALUE (0/50°C) : 3600K ± 1%
3. OPERATING TEMPERATURE RANGE : -40°C TO +250°C.
4. THERMAL TIME CONSTANT : 15SEC IN WATER
5. VOLTAGE BREAKDOWN STRENGTH : 1500V AC FOR 3SEC.
6. INSULATION RESISTANCE : A MINIMUM OF 100MΩ @ 500VOLTS DC.
7. DISSIPATION FACTOR : 1mW/°C.
8. LASER MARKING "MOLEX-DATE CODE(MM/YY)"

SS HOUSING DETAILS:



FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
	DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex							
	mm		NTS												
	GENERAL TOLERANCES (UNLESS SPECIFIED)							GLASS NTC MOUNTING -10K±1%,B3600,L100							
	ANGULAR TOL ± °														
	4 PLACES		±												
	DIVISIONAL SYMBOLS	3 PLACES		±		EC NO: 721031		2022/09/13		PRODUCT CUSTOMER DRAWING					
		2 PLACES		±		DRWN: NANDAK		2022/09/15							
		1 PLACE		±		CHK'D: RBBHASKAR		2022/09/15							
		0 PLACES		±		APPR: RBBHASKAR		2022/09/15							
INITIAL REVISION:				DOCUMENT NUMBER		DOC TYPE		DOC PART				REVISION			
DRWN: RAVIKM				2022/01/28		2185343617		PSD		000		B2			
APPR: RBBHASKAR				2022/02/10											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						A3-SIZE		218534		2185343617		GENERAL MARKET		1 OF 2	

