

REVISIONS									
REV	ECO	DESCRIPTION	DATE	BY	APPR				
A1	-	RELEASE NEW DRAWING	01/MAR/22	IAN	TOMMY				





NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:

HOUSING: THERMOPLASTIC; BLACK

SEAL: SILICONE RUBBER

2. MODIFICATIONS: BACKSHELL RING ADAPTER (BRA); REDUCED DIA. WIRE SEAL;

3. SPECIFICATIONS:

- 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
- 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
- 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
- 3.4 MOISTURE RESISTANCE:

IP68(IM OF WATER FOR A PERIOD OF 24 HOURS, MATED


CONDITION);

IP69K(MATED CONDITION)

- 3.5 MATING CYCLE DURABILITY: 100 CYCLES
- 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP02-24-23S\* & AHDP04-24-23S\* ( \* = SEAL TYPE )
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

## 6 CONTACT SIZE AND WIRE RANGE:

CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL	CURRENT
SIZE	O.D.	O.D.	WIRE RANGE	RATING
16	1.35 mm (.053 in)	3.05 mm (.120 in)	14-20 AWG (2.0-0.5mm²)	13 AMPS



BACKSHELL RING ADAPTER -BLUE

AHDP06-24-2		4-23PR-	-BRA		REF:HDP26-24-23PE-L017				
QUANTITY	ITITY PART NUMBER		₹	DESCRIPTION				ITEM	
			MAT	ERI	٩LS	3 LI	ST		
1 PL DEC ±0.30   Fractions +1/64		SIGN	NATURES	S DATE A SO IS A SO IS					
		DRAWN:	IAN.XIAO	01/MAR/22	AR722 Sine Systems - www.amphenol-sine.com 44724 Morley Drive				
		CHECKED:	SULLEN.ZHANG	02/MAR/22				_	
3) Note reference	Note reference = X								
MATERIAL SPECIFICATIONS:  WEIGHT: 57.7g  PROCESS SPECIFICATIONS:		APPROVAL:	TOMMY.XIE	03/MAR/22			Clinton Township, MI 48036		
		CUSTOMER:  THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA. SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAI		23POS,PLUG,SOCKET,24SZ,					
				RD SEAL,BRA,DURAMATE AHDP					
				B	C-	AHDP06-24-23PR-BR	1	visio 1	
NEXT ASS'Y:			RING VARIATIONS	S.	SCALE: N	ONE	DURAMATE SHEET 1	OF	1