

1 7/16-12 UN THREAD

M5X0.8-6H 8mm(2X) DEEP THREADED INSERT

50.8±0.50 Ø38.1 Ø33.8

RECOMMENDED TORQUE VALUES:1.9-2.2 N.m



1. MATERIAL:

HOUSING: THERMOPLASTIC; BLACK

SEAL: SILICONE RUBBER

THREADED INSERT: STAINLESS STEEL

2. MODIFICATIONS: WIDE THREAD ADAPTER(WAT); STANDARD DIA, WIRE SEAL;


SEALED PANEL MOUNT:

72.8±0.50

- 3. SPECIFICATIONS:
 - 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
 - 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
 - 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
 - 3.4 MOISTURE RESISTANCE: IP67&IP69K (MATED CONDITION).
 - 3.5 MATING CYCLE DURABILITY: 100 CYCLES
 - 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP06-18-08S* (* = SEAL TYPE)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.




CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL	CURRENT
SIZE	O.D.	O.D.	WIRE RANGE	RATING
12	3.43 mm (.135 in)	4.32 mm (.170 in)	10-14 AWG (8.0-2.0mm²)	



MOUNTING HOLE

RECOMMENDED PANEL THICKNESS:1.6 TO 4.7MM



	AIIDI 02-1	J-001 14-	*****						
	PART N	IUMBER	₹ .			DE	SCRIPTION		m
QUANTITY			MAT	ERI	ALS	3 LI	ST		
	WISE SPECIFIED	1918	VATURES	DATE					T
All dimensions a Tolerances are a PL DEC ±0.30		DRAWN:	NTOTA	15JUL20	Ampheno)
2 PL DEC ±0.15 3 PL DEC ±0.08	Angles ±1°	CHECKED:	ORIONLI	17JUL20		Sin	ne Systems - www.amphe	enol-sine.com	
3) Note reference = X		ENGINEER:			44724 Morley Drive Clinton Township, MI 48036				
MATERIAL SPECIFICA	TIONS:	APPROVAL:	TOMMY.XIE	20JUL20			Clinton Township, MI 40	8036	
		CUSTOMER:				8	8 POS, RECEPTAC	LE, PIN,	
			IG IS SUPPLIED		PAN	ELMAT	E AHDP SIZE 18, N	ORMAL SE	EAL, WT
		SPECIFICATION SHOWN HERE THE AMPHEN OF REPRODU	ONS AND PERFO EON ARE THE PI IOL CORPORATI JCTION ARE IMP ARE SUBJECT 1	ORMANCE DATA ROPERTY OF ION. NO RIGHTS PLIED. ALL	B	C-	AHDP02-18-0	8PN-WT	A A
			RING VARIATION	NS.	SCALE: N	ONE		SHEET 1	or 1

AHDP02-18-08PN-WTA

TITLE: 8 POS, RECEPTACLE, PIN, PANELMATE AHDP SIZE 18, NORMAL SEAL, WTA AHDP02-18-08PN-WTA

REV:

TEM

SHEET 1 OF

ATP Series™ - Contact Size 12 Options

Machined Contacts, Sockets & Pins						
Part Number Description		Size	AWG	Туре		
AT60-204-12141-10	0-204-12141-10 Male Contact - Pin, Nickel-plated		10-12	Machined		
AT62-203-12141-10 Female Contact - Socket, Nickel-plated		12	10-12	Machined		
AT60-220-1231 Male Contact - Pin, Gold-plated		12	12-14	Machined		
AT62-210-1231	Female Contact - Socket, Gold-plated	12	12-14	Machined		
AT60-204-12141	Male Contact - Pin, Nickel-plated	12	12-14	Machined		
AT62-203-12141	Female Contact - Socket, Nickel-plated	12	12-14	Machined		

DiagnosticGrade™ Machined Contacts, Sockets & Pins • Smaller AWG for Diagnostic Applications • Gold-plated • Increased Mating Cycles • Cost-effective					
Part Number	Description	Size	AWG	Туре	
65-54749	Male Contact - DiagnosticGrade™, Pin, Gold-plated	12	20	Machined	
AT62-210-1231-1820	Female Contact - DiagnosticGrade™, Socket, Gold-plated	12	20	Machined	

Tooling - Machined Contacts				
Part Part Number		Description		
	CA-5D12	Universal Hand Crimp Tool, Size 12/16/20 (Machined contacts only)		
33	CA-5E12	Pneumatic Crimp Tool, Size 12/16/20 (Machined contacts only)		

Contact Removal Tools				
Part	Part Number	Description		
refer turbs	ATRT-100	Used for removal of contacts for A Series™ products		
	AT11-337-1205	Contact Removal Tool, Plastic, Size 12		
	A114017	Sealing Plug, Size 12, White		

Stamped & Formed Contacts, Sockets & Pins							
Part Number Description			AWG	Туре			
AT60-12-0244	Male Contact - Pin, Gold-plated	12	10-12	Stamped & Formed			
AT62-12-0244	Female Contact - Socket, Gold-plated	12	10-12	Stamped & Formed			
AT60-12-0222 Male Contact - Pin, Nickel-plated		12	10-12	Stamped & Formed			
AT62-12-0222 Female Contact - Socket, Nickel-plated		12	10-12	Stamped & Formed			
AT60-12-0144 Male Contact - Pin, Gold-plated		12	12-14	Stamped & Formed			
AT62-12-0144 Female Contact - Socket, Gold-plated		12	12-14	Stamped & Formed			
AT60-12-0166 Male Contact - Pin, Nickel-plated		12	12-14	Stamped & Formed			
AT62-12-0166 Female Contact - Socket, Nickel-plated			12-14	Stamped & Formed			

Tooling - Stamped & Formed Contacts					
Part	Part Number Description				
	MFX-3973	Crimp Die - Size 12 (S&F contacts only)			
	MFX-3985	Crimp Die - Size 12 (S&F contacts only) 10-12AWG -02XX Series			
	ATT-12-00	Hand Crimp Tool - Size 12, 12AWG (S&F contacts only)			

Amphenol Sine Systems 44724 Morley Drive Clinton Township, MI 48036 USA www.amphenol-sine.com 09/2021