

NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:

HOUSING: THERMOPLASTIC; BLACK

SEAL: SILICONE RUBBER

2. MODIFICATIONS: BACKSHELL RING ADAPTER (BRA);

REDUCED DIA. WIRE SEAL

3. SPECIFICATIONS:

3.1 OPERATING TEMPERATURE: -55°C TO +125°C.

3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.

3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.

3.4 MOISTURE RESISTANCE:

IP68(IM OF WATER FOR A PERIOD OF 24 HOURS, MATED

-SIZE 12 CONTACTS

(8 PLACES) 6

CONDITION);

IP69K(MATED CONDITION).

3.5 MATING CYCLE DURABILITY: 100 CYCLES


3.6 RoHS COMPLIANT

4. MATING PART: AHDP02-18-08P\* & AHDP04-18-08P\* ( \* = SEAL TYPE )

5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

6 CONTACT SIZE AND WIRE RANGE:

CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL	CURRENT
SIZE	O.D.	O.D.	WIRE RANGE	RATING
12	2.46 mm (.097 in)	4.01 mm (.158 in)	10-14 AWG (6.0-2.0mm²)	25 AMPS



BACKSHELL RING ADAPTER - BLUE

	AHDP06-1	8-08SR-BRA		REF:HDP26-18-8SE-L017					
QUANTITY	PART NUMBER			DESCRIPTION				ITEM	
		ı	MAT	ERI	٩LS	S LI	ST		
UNLESS OTHERWISE SPECIFIED		SIGNATURES		DATE	Amphenol				
All dimensions a Tolerances are a PL DEC ±0.30		DRAWN:	MILO	30/MAR/22		$\vdash$	mpne		ı
2 PL DEC ±0.35 3 PL DEC ±0.08 Angles ±1°		CHECKED:	SULLEN	31/MAR/22	Sine Systems - www.amphenol-sine.com				
		ENGINEER:			44724 Morley Drive Clinton Township, MI 48036				
MATERIAL SPECIFICA	TIONS:	APPROVAL:	TOMMY	01/APR/22			Clinton Township, Wi 46	030	
WEIGHT: 47.5g		CUSTOMER:			8POS, PLUG, SOCKET, SIZE 18,				
		SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL		RD SEAL, BRA, DURAMATE AHDP					
PROCESS SPECIFICATIONS:				B	C-	AHDP06-18-0	8SR-BRA	A A1	
NEXT ASS'Y:				SCALE: N	ONE	DURAMATE	sнеет <b>1</b>	of <b>1</b>	