




Pushing Performance  
Since 1945

## Han M12 Crimp D-coded female metal nut



Part number	09 14 881 2406
Specification	Han M12 Crimp D-coded female metal nut
HARTING eCatalogue	<a href="https://b2b.harting.com/09148812406">https://b2b.harting.com/09148812406</a>

### Identification

Category	Inserts
Series	Han-Modular®
Specification	With metal nut

### Version

Termination method	Crimp termination
Gender	Female
Number of contacts	4
further contacts	+ shielding
Coding	D-coding
Details	Please order crimp contacts separately.

### Technical characteristics

Conductor cross-section	0.13 ... 0.82 mm <sup>2</sup>
Conductor cross-section	AWG 26 ... AWG 18
Wire outer diameter	≤2.3 mm
Rated current	4 A
Rated voltage	32 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Insulation resistance	>10 <sup>8</sup> Ω



Pushing Performance  
Since 1945

## Technical characteristics

Contact resistance	≤10 mΩ
Contact resistance, shielding	≤100 mΩ
Tightening torque	0.6 Nm
Wrench size	12 13
Limiting temperature	-40 ... +85 °C
Mating cycles	≥500

## Material properties

Material (insert)	Liquid crystal polymer (LCP)
Material (shielding)	Copper alloy, nickel plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	1
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140187795
eCl@ss	27440205 Contact insert for industrial connectors