

Recommended Mounting Hole

Dimensions : Millimetres

Specifications:

Electrical Performance:	
Impedance	: 50Ω.
Frequency range	: DC to 6.0GHz.
Maximum working voltage	: 60V rms.
Minimum dielectric withstanding voltage	: 200V rms.
Minimum insulation resistance	: 500MΩ.

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for	TOLERANCES:	DRAWN BY:	DATE:	DRAWING TITLE:			
information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change with- out notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the prod- ucts for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or	UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	Ramya	19/06/09	N Type - U.FL Cable - IP67, 200mm			
		CHECKED BY:	DATE:	SIZE DWG NO.	M10002260	ELECTRONIC FILE	REV
		Suresh	19/06/09			1714792-TDS DWG	A
		APPROVED BY:	DATE:				<u> </u>
or restrict the Group's liability for death or personal injury resulting from its negligence. SPC MULTICOMP is the registered trademark of the Group. © Premier Famell plc 2009.		Farnell	03/07/09	SCALE: NTS	U.O.M.: mm	SHEET: 1 OI	F 2

multicomp	PART NO.		REVISIONS								
	R-632G7210200CE	ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
		-	А	RELEASED	Ramya	19/06/09	Suresh	19/06/09	Farnell	03/07/09	

Specification Table

ltem	Description	Part Number
1	N Bulkhead Jack, Crimp Type, For \01.37mm Cable	
2	Heat Shrink Tube F32, Black ø3.0mm, L = 15.0mm	
3	φ1.37mm Cable, (Colour: Black)	R-632G7210200CE
4	HRS U.FL-LP-088 Shell for	
5	HRS U.FL-LP-088 Contact Terminal for ϕ 1.37mm Cable	

http://www.farnell.com

http://www.newark.com

http://www.cpc.co.uk

(the "croup") or are incensed to it. No licence is granted for the use or it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change with- out notice and replaces all data sheets previously supplied. The Information supplied is in the product of the supervision of the supplied of the information supplied is a supplied of the information supplied is an end of the supplied of the supervision of the supplied. The Information supplied is a supplied of the supplied is a supplied of the supplied of the supplied is a supplied of the supplied of the supplied is a supplicit of the supplicit of the supplied of the supplied of the supplicit o	TOLERANCES:	DRAWN BY:	DATE:	DRAWING TITLE:				
	ge with- pplied is cy or SPECIFIED, of this luded or ion or ware of to limit gence.	Ramya	19/06/09	N Type - U.FL Cable - IP67, 200mm				
		CHECKED BY:	DATE:	SIZE DWG NO.		ELECTRONIC FILE	REV	
data sheet should check for themselves the Information and the suitability of the prod- ucts for their purpose and not make any assumptions based on information included or		Suresh	19/06/09		M10002260	1714792-TDS DWG	Α	
omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the new life of the second		APPROVED BY:	DATE:				<u> </u>	
the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC MULTICOMP is the registered trademark of the Group. © Premier Famel plc 2009.		Farnell	03/07/09	SCALE: NTS	U.O.M.: mm	SHEET: 2 O	F 2	