

NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:

HOUSING: THERMOPLASTIC; BLACK

SEAL: SILICONE RUBBER

2. MODIFICATIONS: BACKSHELL RING ADAPTER (BRA);

STANDARD DIA. WIRE SEAL;

- 3. SPECIFICATIONS:
 - 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
 - 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
 - 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
 - 3.4 MOISTURE RESISTANCE:


IP68(IM OF WATER FOR A PERIOD OF 24 HOURS, MATED CONDITION);


IP69K(MATED CONDITION).

- 3.5 MATING CYCLE DURABILITY: 100 CYCLES
- 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP02-18-21S* & AHDP04-18-21S* (* = SEAL TYPE)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
- 6 CONTACT SIZE AND WIRE RANGE:

CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL	CURRENT
SIZE	O.D.	O.D.	WIRE RANGE	RATING
20	1.02 mm (.040 in)	2.41 mm (.095 in)	16-22 AWG (1.5-0.5mm²)	

	REVISIONS									
REV	ECO	DESCRIPTION	DATE	BY	APPR					
A1	-	RELEASE NEW DRAWING	31/MAR/22	MILO	TOMMY					





	AHDP06-18-21PN-BRA			REF:HDP26-18-21PN-L017				
QUANTITY PART N		NUMBER		DESCRIPTION		ITEM		
		ı	MA	[ERI	ALS LIST	•		
UNLESS OTHERWISE SPECIFIED		SIGNATURES		S DATE	Amphonol			
All dimensions a Tolerances are a PL DEC ±0.30	0.30 Fractions ±1/64 0.15 Angles ±1°	DRAWN:	MILO	31/MAR/22	Amphenol			
2 PL DEC ±0.15 3 PL DEC ±0.08		CHECKED:	SULLEN	01/APR/22	Sine Systems - www.amphenol-sine.com			
i) Note reference = X		ENGINEER:			44724 Morley Drive			
MATERIAI SPECIFICA	TIONS:	APPROVAL:	TOMMY	02/APR/22	Clinton Township, MI 48036			
WEIGHT: 45.5g PROCESS SPECIFICATIONS: NEXT ASSY:		CUSTOMER:			21POS, PLUG, PIN, SIZE 18,			
		SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL			NORMAL SEAL, BRA, DURAMATE AHDP			
				FORMANCE DATA PROPERTY OF TION. NO RIGHTS IPLIED. ALL	B C- AHDP06-18-21PN-BRA	REVISION A		
				ONS.	SCALE: NONE DURAMATE SHEET 1 OF	1		